


# PRODUCT DATA SHEET

Part Number : **1921XX5W**

| Type | Size | IP Rating | Description                 |
|------|------|-----------|-----------------------------|
| LED  | M14  | 67        | Round bezel panel indicator |

Dimensions(mm):



| Part #   | Colour     | Voltage | Current(mA) | Intensity(mcd typ) |
|----------|------------|---------|-------------|--------------------|
| 1921X25W | Cool white | 12Vdc   | 20          | 500                |
| 1921X35W | Cool white | 24Vdc   | 20          | 500                |

Notes:

1. Bezel codes : X=0(satin),1(black),or 2(matt) chrome
2. Storage temperature -25 °C to +80°C
3. Application temperature -20 °C to +60°C
4. Terminals: Brass +ve, Tinned brass -ve
5. Terminals not qualified for soldering
6. The plastic(polycarbonate) has limited chemical resistance
7. Sealed to IP67 when used with the supplied gasket
8. RoHS & REACH SVHC compliant

Issue # 1 : 13 Feb 12