

OSLO-CLUSTER-W-OSL LENS FOR OSRAM OSOLON



- Designed & optimized for Osram's Osolon SSL LED Clusters
- Lens material optical grade PMMA with high UV and temperature resistance (105°C/220°F). Allows use of high current and temperature conditions
- Comes with position pins
- Check fastening details from this link
(http://www.ledil.com/datasheets/DataSheet_GLUES.pdf)

LENS TYPES

NAME	ORDERING CODE	FWHM Angle
Oslo-7-W	F11355_Oslo-7-W-OSL	±32°

© Ledil Oy – PRELIMINARY - Subject to change without prior notice



Ledil Oy
Tehdaskatu 13
FIN-24100 SALO, Finland

www.ledil.com
email: ledil@ledil.com
FAX: +358-2-733 8001

2010-10-13

MEASUREMENTS

Relative intensity of F11355_Oslo-7-W-OS




© Ledil Oy – PRELIMINARY - Subject to change without prior notice

Ledil Oy
Tehdaskatu 13
FIN-24100 SALO, Finland

www.ledil.com
email: ledil@ledil.com
FAX: +358-2-733 8001

2010-10-13

DRAWINGS



© Ledil Oy – PRELIMINARY - Subject to change without prior notice

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Ledil:

[F11355_Oslo-Cluster-W-OSL](#)