




MATERIALS:

Body and Fittings:

- Shell - Brass, Tarnish Resistant Plating
- Center Contact - Gold Plated Phosphor Bronze
- Dielectric - PTFE

RATING:

Operating Voltage: Shield/Earth: 30VAC/60VDC Max.

Inner Conductor/Shield: 500VRMS Max.

Operating Temperature: -55°C to +85°C (-67°F) (+185°F)

Nominal Impedance: Non-Constant Impedance.

ORDERING INFORMATION: Model 3287

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

10/11/00

SY/EH/LS

S:\Engineering\Release\DataSheets\FlukeDataSheet\3287_1_01.doc

Sales: 800-490-2361 Fax: 888-403-3360

Technical Assistance: 800-241-2060

Last saved by PN

PomonaACCESS 90183 (800) 444-6785 or (425) 446-6010

More drawings available at www.pomonaelectronics.com

Page 1 of 1