

AULT SPECIFICATIONS

30-40VA Wall Plug Series

INPUT

Voltage	120 VAC
Line Frequency	60 Hz
Configuration	North American Wall Plug, No Ground

OUTPUT

<i>Model Number</i>	<i>Rated Output Volts AC</i>	<i>Output Current Amps</i>	<i>Max VA</i>
T57-084000-A000C	8	4.00	32.0
T57-122400-A000G	12	2.40	29.0
T57-142500-A000G	14	2.50	35.0
T57-182200-A000G	18	2.20	40.0
T57-201500-A000G	20	1.50	30.0

ELECTRICAL

Topology	Step Down AC/AC Transformer
Dielectric Withstand	1500 VAC primary-secondary
Protection	Current, Thermal or Energy Limiting
EMI	Meets FCC Class B
CE	NA

SAFETY APPROVALS

UL1310, CSA22.2-223

ENVIRONMENTAL

Operating Temperature	0° to 40° C with no derating
Storage Temperature	-30° to +85° C
Relative Humidity	5% to 95% non-condensing
Altitude	0 - 10,000 feet
Cooling	Convectional non-vented case

MECHANICAL

Case and Dimensions	T57 - North American Wall Plug 86 L X 69 W X 56 H (mm) 3.4 L X 2.7 W X 2.2 H (in)
Case Material	Black 94V1 Polycarbonate
Weight	27 ounces, 760 grams, (excluding cord)
Cord and Connectors	6 Ft., 2 Conductor, 18-20 AWG, Ault #3 Connector Other connectors are also available

WARRANTY

1 Year