


1 2 3 4 5

A B C D E F G H

ALL DIMENSIONS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC. U.S. PATENT OFFICE. NO REPRODUCTION, COPIED, OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.



WIRE DIAGRAM	
P1	P2
1	GRAY
2	ORANGE
3	BLACK
4	RED
5	GREEN
6	YELLOW
7	BLUE
8	BROWN

CUSTOMER APPROVAL
ENGR. SIGN Matt Lerner
DATE: 4-13-99

- NOTES: UNLESS OTHERWISE SPECIFIED.
1. TEST CABLE FOR ALL OPENS & SHORTS.
 2. PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG. PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.

488-148-505-D	121-810-022	14.0 FT (4.3 M)	50.0 IN (1270.0 MM)	WHITE
488-148-504-D	121-810-012	14.0 FT (4.3 M)	50.0 IN (1270.0 MM)	BLACK
488-148-503-D	121-810-002	14.0 FT (4.3 M)	50.0 IN (1270.0 MM)	SILVER SATIN
488-108-502-D	121-810-021	10.0 FT (3.0 M)	42.0 IN (1066.8 MM)	WHITE
488-108-501-D	121-810-011	10.0 FT (3.0 M)	42.0 IN (1066.8 MM)	BLACK
488-108-500-D	121-810-001	10.0 FT (3.0 M)	42.0 IN (1066.8 MM)	SILVER SATIN
488-078-505-D	121-810-020	7.0 FT (2.1 M)	28.0 IN (711.2 MM)	WHITE
488-078-504-D	121-810-010	7.0 FT (2.1 M)	28.0 IN (711.2 MM)	BLACK
488-078-503-D	121-810-000	7.0 FT (2.1 M)	28.0 IN (711.2 MM)	SILVER SATIN
488-058-502-D	121-810-023	5.0 FT (1.5 M)	22.0 IN (558.8 MM)	WHITE
488-058-501-D	121-810-013	5.0 FT (1.5 M)	22.0 IN (558.8 MM)	BLACK
488-058-500-D	121-810-003	5.0 FT (1.5 M)	22.0 IN (558.8 MM)	SILVER SATIN
IOI PART NUMBER	IOI CABLE PART NUMBER	EXTENDED LENGTH "X"	RETRACTED LENGTH "R"	

TABULATION BLOCK


I/O INTERCONNECT SANTA ANA, CALIFORNIA	
THIRD ANGLE PROJECTION	REVERSE STYLE, CABLE ASSEMBLY
UNLESS OTHERWISE NOTED: 1) DIMENSIONS ARE IN INCHES (MILLIMETERS) 2) TOLERANCES: X.XX ± 0.25 (6.35)	REVERSE STYLE, CABLE ASSEMBLY
MODULAR COIL CABLE, 26 AWG (7/34) BARE COPPER, 8 CONDUCTOR, UNSHIELDED, PVC JACKET, (SEE TABULATION BLOCK FOR COLOR).	REVERSE STYLE, CABLE ASSEMBLY
CONNECTOR, MODULAR PLUG, 8 POSITION, 8 CONDUCTOR, 50U" AU, FLAT TYPE EXIT.	REVERSE STYLE, CABLE ASSEMBLY
DESCRIPTION	REVERSE STYLE, CABLE ASSEMBLY
CABLE ASSEMBLY PARTS LIST	REVERSE STYLE, CABLE ASSEMBLY

A B C D E F G H


THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC. NO PARTS SHALL BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT THE WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.

DWG. NO.	REV.	DESCRIPTION	DATE	APPROVED
XXB-502-D	X1	CUSTOMER APPROVAL	03/24/99	E.V.

1



2



3



CUSTOMER APPROVAL

ENGR. SIGN Math. Neme

DATE: 4-12-99

NOTES: UNLESS OTHERWISE SPECIFIED.

1. CABLE TO BE BUNDLED AND TWIST TIED.
2. TEST CABLE FOR ALL OPENS & SHORTS.
3. PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG. PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.

5


ITEM	QTY	MFG.	IDI PART NO.	DESCRIPTION
2	*X	IDI	120-810-020	MODULAR CABLE, 26 AVG (7/34) BARE COPPER, 8 CONDUCTOR, UNSHIELDED, WHITE PVC.
1	2 PCS	IDI	325-881-50X	CONNECTOR, MODULAR PLUG, 8 POSITION, 8 CONDUCTOR, 50u" AU, FLAT TYPE EXIT.

CABLE ASSEMBLY PARTS LIST

H2881-25-ND
H2881-14 ND
H2881-07-ND

488-258-502-D	25.0 FT ± 4.0 IN 7.62 M ± 101.6 MM
488-148-502-D	14.0 FT ± 3.0 IN 4.27 M ± 76.2 MM
488-078-502-D	7.0 FT ± 2.0 IN 2.13 M ± 50.8 MM
PART NUMBER	LENGTH *X

I/O INTERCONNECT	
SANTA ANA, CALIFORNIA	
DATE	REV.
03/24/99	X1





THIRD ANGLE PROJECTION

UNLESS OTHERWISE NOTED:
1) DIMENSIONS ARE IN INCHES (MILLIMETERS)
2) TOLERANCES
XXX ± 0.25 (6.35)

TITLE	
BPBP MODULAR, REVERT STYLE, WHITE, CABLE ASSEMBLY	
DATE	REV.
03/24/99	X1
SCALE: NONE	
SHEET 1 OF 1	

A B C D E F G H
 DWG. NO. ZONE REV. DESCRIPTION DATE APPROVED
 XXB-510-D XI 1 CUSTOMER APPROVAL 03/24/99 E.V.



CUSTOMER APPROVAL
 ENGR. SIGN Matt Jones
 DATE: 4-12-99

H1883-25-ND
 H1883-14-ND
 H1883-07-ND

- NOTES: UNLESS OTHERWISE SPECIFIED.
1. CABLE TO BE BUNDLED AND TWIST TIED.
 2. TEST CABLE FOR ALL OPENS & SHORTS.
 3. PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG. PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.

ITEM	QTY	MFG.	IOI PART NO.	DESCRIPTION
2	"X"	IOI	120-810-000	MODULAR CABLE, 26 AWG (7/34) BARE COPPER, 8 CONDUCTOR, UNSHIELDED, SILVER SATIN PVC.
1	2 PCS	IOI	325-881-50X	CONNECTOR, MODULAR PLUG, 8 POSITION, 8 CONDUCTOR, 50u" AU, FLAT TYPE EXIT.
CABLE ASSEMBLY PARTS LIST				

THIRD ANGLE PROJECTION		UNLESS OTHERWISE NOTED: 1) DIMENSIONS ARE IN INCHES (MILLIMETER) 2) TOLERANCES: X.XX ± 0.25 (6.35)
------------------------	--	---

PART NO. 488-258-510-D 488-148-510-D 488-078-510-D	PART NUMBER I/O INTERCONNECT	LENGTH "X" 25.0 FT ± 4.0 IN 7.62 M ± 101.6 MM 14.0 FT ± 3.0 IN 4.27 M ± 76.2 MM 7.0 FT ± 2.0 IN 2.13 M ± 50.8 MM
---	---------------------------------	--

TITLE I/O INTERCONNECT SANTA ANA, CALIFORNIA	BUREAU BFBP MODULAR, STANDARD STYLE SILVER SATIN, CABLE ASSEMBLY
PART NO. 488-XXB-510-D	PART NO. 488-XXB-510-D
CUSTOMER DIGI KEY	REV. XI
SCALE NONE	SHEET 1 OF 1


A B C D E F G H

THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC., U.S.A. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.

DWG. NO.	ZONE	REV.	DESCRIPTION	DATE	APPROVED
XX8-511-D		X1	CUSTOMER APPROVAL	03/24/99	E.V.

WIRE DIAGRAM

P1		P2
1	GRAY	8
2	ORANGE	7
3	BLACK	6
4	RED	5
5	GREEN	4
6	YELLOW	3
7	BLUE	2
8	BROWN	1



CUSTOMER APPROVAL
ENGR. SIGN Math Nemeo
DATE: 4-12-99


H1882-25-ND
H1882-14-ND
H1882-07-ND

- NOTES: UNLESS OTHERWISE SPECIFIED.
- CABLE TO BE BUNDLED AND TWIST TIED.
 - TEST CABLE FOR ALL OPENS & SHORTS.
 - PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG. PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.

PART NUMBER	LENGTH "X"
488-258-511-D	25.0 FT ± 4.0 IN 7.62 M ± 101.6 MM
488-148-511-D	14.0 FT ± 3.0 IN 4.27 M ± 76.2 MM
488-078-511-D	7.0 FT ± 2.0 IN 2.13 M ± 50.8 MM

I/O INTERCONNECT SANTA ANA, CALIFORNIA	
DATE	03/24/99
DESIGNED BY	BP8P
CHECKED BY	BP8P
APPROVED BY	BP8P
TITLE	BP8P MODULAR, STANDARD STYLE, BLACK, CABLE ASSEMBLY
PART NO.	488-XX8-511-D
DWG. NO.	488-XX8-511-D
CUSTOMER	DIGI KEY
SCALE	NONE
SHEET	1 OF 1

ITEM	QTY	MFG.	IDT PART NO.	DESCRIPTION
2	"X"	IDT	120-810-010	MODULAR CABLE, 26 AWG (7/34) BARE COPPER, 8 CONDUCTOR, UNSHIELDED, BLACK PVC.
1	2 PCS	IDT	325-881-50X	CONNECTOR, MODULAR PLUG, 8 POSITION, 8 CONDUCTOR, 50u" Au, FLAT TYPE EXIT.
CABLE ASSEMBLY PARTS LIST				



CUSTOMER APPROVAL
ENGR. SIGN Math Amec
DATE: 4-12-99

NOTES: UNLESS OTHERWISE SPECIFIED.
1. CABLE TO BE BUNDLED AND TWIST TIED.
2. TEST CABLE FOR ALL OPENS & SHORTS.
3. PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG.
PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.


THIRD ANGLE PROJECTION		I/O INTERCONNECT SANTA ANA, CALIFORNIA		BPBP MODULAR, REVERT STYLE, BLACK, CABLE ASSEMBLY	
UNLESS OTHERWISE NOTED: 1) DIMENSIONS ARE IN INCHES (MILLIMETER) 2) TOLERANCES: XXX ± 0.25 (6.35)		PART NO. 488-XXB-501-D		REV. X1	
DRAWING NO. 488-XXB-501-D		CUSTOMER DIGI KEY		SCALE NONE	
SHEET 1 OF 1		LENGTH 'X'		LENGTH 'X'	

2	*X*	101	120-810-010	MODULAR CABLE, 26 AWG (7/34) BARE COPPER, 8 CONDUCTOR, UNSHIELDED, BLACK PVC.
1	2 PCS	101	325-881-50X	CONNECTOR, MODULAR PLUG, 8 POSITION, 8 CONDUCTOR, 50u" AW, FLAT TYPE EXIT.
ITEM	QTY	MFG.	IOI PART NO.	DESCRIPTION

CABLE ASSEMBLY PARTS LIST

THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC. NO PART OF THIS DOCUMENT MAY BE REPRODUCED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.

A		B		C		D		E		F		G		H	
DWG. NO.		ZONE		REV.		DESCRIPTION		DATE		APPROVED		E.V.			
XXB-500-D				X1		CUSTOMER APPROVAL		03/24/99							



CUSTOMER APPROVAL
ENGR. SIGN 4 Matt Jensen
DATE: 4-17-99

- NOTES: UNLESS OTHERWISE SPECIFIED.
- CABLE TO BE BUNDLED AND TWIST TIED.
 - TEST CABLE FOR ALL OPENS & SHORTS.
 - PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG. PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.



488-258-500-D	250 FT ± 4.0 IN 762 M ± 101.6 MM
488-148-500-D	140 FT ± 3.0 IN 427 M ± 76.2 MM
488-078-500-D	70 FT ± 2.0 IN 213 M ± 50.8 MM
PART NUMBER I/O INTERCONNECT	
LENGTH 'X'	

THIRD ANGLE PROJECTION				I/O INTERCONNECT			
UNLESS OTHERWISE NOTED: 1) DIMENSIONS ARE IN INCHES (MILLIMETER) 2) TOLERANCES: XXX ± 0.25 (6.35)				SANTA ANA, CALIFORNIA			
MODULAR CABLE, 26 AVG (7/34) BARE COPPER, 8 CONDUCTOR, UNSHIELDED, SILVER SATIN PVC.				BPBP MODULAR, REVERT STYLE, SILVER SATIN, CABLE ASSEMBLY			
CONNECTOR, MODULAR PLUG, 8 POSITION, 8 CONDUCTOR, 50U" AU, FLAT TYPE EXIT.				PART NO. 488-XXB-500-D			
DESCRIPTION				REV. NO. 488-XXB-500-D			
CABLE ASSEMBLY PARTS LIST				CUSTOMER DIGI KEY			
				SCALE: NONE			
				SHEET 1 OF 1			

A		B	C	D	E	F	G	H
DWG. NO.		ZONE	REV.	DESCRIPTION		DATE	APPROVED	
XXB-521-D			X1	CUSTOMER APPROVAL		03/24/99	E.V.	

THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC. AND ARE NOT TO BE REPRODUCED OR USED IN ANY MANNER WITHOUT THE WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.

1



1 2 PCS

P1

OPEN END

WIRE DIAGRAM

P1	OPEN END
1	GRAY
2	ORANGE
3	BLACK
4	RED
5	GREEN
6	YELLOW
7	BLUE
8	BROWN

3



CUSTOMER APPROVAL
ENGR. SIGN Math Nemes
DATE: 4-12-99

H3882-25-ND
H3882-14-ND
H3882-07-ND

NOTES: UNLESS OTHERWISE SPECIFIED.

- CABLE TO BE BUNDLED AND TWIST TIED.
- TEST CABLE FOR ALL OPENS & SHORTS.
- PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG. PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.

488-258-521-D	25.0 FT ± 4.0 IN 7.62 M ± 101.6 MM
488-148-521-D	14.0 FT ± 3.0 IN 4.27 M ± 76.2 MM
488-078-521-D	7.0 FT ± 2.0 IN 2.13 M ± 50.8 MM

PART NUMBER
I/O INTERCONNECT

LENGTH "X"

THIRD ANGLE PROJECTION



I/O INTERCONNECT

SANTA ANA, CALIFORNIA



UNLESS OTHERWISE NOTED:
1) DIMENSIONS ARE IN INCHES (MILLIMETER)
2) TOLERANCES:
XXX ± 0.25 (6.35)

MODULAR CABLE, 26 AVG (7/34) BARE COPPER, 8 CONDUCTOR, UNSHIELDED, BLACK PVC.

CONNECTOR, MODULAR PLUG, 8 POSITION, 8 CONDUCTOR, 50u" AU, FLAT TYPE EXIT.

DESCRIPTION

CABLE ASSEMBLY PARTS LIST

5


ITEM	QTY	MFG.	ID1 PART NO.	DESCRIPTION
2	"X"	ID1	120-810-010	MODULAR CABLE, 26 AVG (7/34) BARE COPPER, 8 CONDUCTOR, UNSHIELDED, BLACK PVC.
1	1 PC	ID1	325-881-50X	CONNECTOR, MODULAR PLUG, 8 POSITION, 8 CONDUCTOR, 50u" AU, FLAT TYPE EXIT.
CABLE ASSEMBLY PARTS LIST				
REV.		SCALE		SHEET 1 OF 1
X1		NONE		

A	B	C	D	E	F	G	H
DWG. NO.	ZONE	REV.	DESCRIPTION	DATE	APPROVED		
XXB-520-D		X1	CUSTOMER APPROVAL	03/24/99	E.V.		

THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC. NO PARTS OR MATERIALS ARE TO BE USED IN ANY MANNER WITHOUT THE WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.

WIRE DIAGRAM

PI	OPEN END
1	GRAY
2	ORANGE
3	BLACK
4	RED
5	GREEN
6	YELLOW
7	BLUE
8	BROWN



CUSTOMER APPROVAL

ENGR. SIGN Math. Armer
DATE: 4-12-99

NOTES: UNLESS OTHERWISE SPECIFIED.

1. CABLE TO BE BUNDLED AND TWIST TIED.
2. TEST CABLE FOR ALL OPENS & SHORTS.
3. PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG. PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.

H3883-25-ND
H3883-14-ND
H3883-67-ND

488-258-320-D	25.0 FT ± 4.0 IN 7.62 M ± 101.6 MM
488-148-320-D	14.0 FT ± 3.0 IN 4.27 M ± 76.2 MM
488-078-320-D	7.0 FT ± 2.0 IN 2.13 M ± 50.8 MM
PART NUMBER	LENGTH "X"
I/O INTERCONNECT	

THIRD ANGLE PROJECTION



UNLESS OTHERWISE NOTED:
1) DIMENSIONS ARE IN INCHES (MILLIMETER)
2) TOLERANCES:
X.XX ± 0.25 (6.35)

I/O INTERCONNECT
SANTA ANA, CALIFORNIA

REV.	REV.	REV.	REV.
1	1	1	1
1	1	1	1
1	1	1	1

MODULAR CABLE, 26 AWG (7/34) BARE COPPER, 8 CONDUCTOR, UNSHIELDED, SILVER SATIN PVC.
CONNECTOR, MODULAR PLUG, 8 POSITION, 8 CONDUCTOR, 50U" AU, FLAT TYPE EXIT.


ITEM	QTY	PI	PI	PI	PI
1	1	1	1	1	1
2	1	1	1	1	1

CABLE ASSEMBLY PARTS LIST

2	"X"	120-810-000	MODULAR CABLE, 26 AWG (7/34) BARE COPPER, 8 CONDUCTOR, UNSHIELDED, SILVER SATIN PVC.
1	1 PC	325-881-50X	CONNECTOR, MODULAR PLUG, 8 POSITION, 8 CONDUCTOR, 50U" AU, FLAT TYPE EXIT.
ITEM	QTY	PI	PI

A		B	C	D	E	F	G	H
DWG. NO.		ZONE	REV.	DESCRIPTION	DATE	APPROVED		
XXB-51X-D			X1	CUSTOMER APPROVAL	03/26/99	E.V.		
			X2	ADD RETRACTED LENGTH	03/29/99	E.V.		

THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC., U.S.A. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.



CUSTOMER APPROVAL
 ENGR. SIGN Math Gerner
 DATE: 4-13-99


- NOTES: UNLESS OTHERWISE SPECIFIED.
1. TEST CABLE FOR ALL OPENS & SHORTS.
 2. PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG. PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.

488-148-515-D	121-810-022	14.0 FT (4.3 M)	50.0 IN (1270.0 MM)	WHITE
488-148-514-D	121-810-012	14.0 FT (4.3 M)	50.0 IN (1270.0 MM)	BLACK
488-148-513-D	121-810-002	14.0 FT (4.3 M)	50.0 IN (1270.0 MM)	SILVER SATIN
488-108-512-D	121-810-021	10.0 FT (3.0 M)	42.0 IN (1066.8 MM)	WHITE
488-108-511-D	121-810-011	10.0 FT (3.0 M)	42.0 IN (1066.8 MM)	BLACK
488-108-510-D	121-810-001	10.0 FT (3.0 M)	42.0 IN (1066.8 MM)	SILVER SATIN
488-078-515-D	121-810-020	7.0 FT (2.1 M)	28.0 IN (711.2 MM)	WHITE
488-078-514-D	121-810-010	7.0 FT (2.1 M)	28.0 IN (711.2 MM)	BLACK
488-078-513-D	121-810-000	7.0 FT (2.1 M)	28.0 IN (711.2 MM)	SILVER SATIN
488-058-512-D	121-810-023	5.0 FT (1.5 M)	22.0 IN (558.8 MM)	WHITE
488-058-511-D	121-810-013	5.0 FT (1.5 M)	22.0 IN (558.8 MM)	BLACK
488-058-510-D	121-810-003	5.0 FT (1.5 M)	22.0 IN (558.8 MM)	SILVER SATIN
101 PART NUMBER	101 CABLE PART NUMBER	EXTENDED LENGTH "X"	RETRACTED LENGTH "R"	

TABULATION BLOCK

8				BROWN				1											
2				"X" FT				101				SEE "TABULATION BLOCK"				MODULAR COIL CABLE, 26 AWG (7/34) BARE COPPER, 8 CONDUCTOR, UNSHIELDED, PVC JACKET, (SEE TABULATION BLOCK FOR COLOR).			
1				2 PCS				101				325-881-50X				CONNECTOR, MODULAR PLUG, 8 POSITION, 8 CONDUCTOR, 50U' AU, FLAT TYPE EXIT.			
ITEM				QTY				MFG.				101 PART NO.				DESCRIPTION			
CABLE ASSEMBLY PARTS LIST																			
I/O INTERCONNECT																			
SANTA ANA, CALIFORNIA																			
TITLE																			
BPBC/BPBC COIL CABLE, STANDARD STYLE, CABLE ASSEMBLY																			
PART NO. 488-XXB-51X-D																			
PWS NO. 488-XXB-51X-D																			
CUSTOMER																			
DIGI KEY																			
REV. X2																			
SCALE: NONE																			
SHEET 1 OF 1																			

THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC., U.S.A. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.



WIRE DIAGRAM

PI	OPEN END
1	GRAY
2	ORANGE
3	BLACK
4	RED
5	GREEN
6	YELLOW
7	BLUE
8	BROWN

CUSTOMER APPROVAL
 ENGR. SIGN Math Ammer
 DATE: 4-13-99

- NOTES: UNLESS OTHERWISE SPECIFIED.
1. TEST CABLE FOR ALL OPENS & SHORTS.
 2. PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG. PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.

488-148-525-D	121-810-022	14.0 FT (4.3 M)	50.0 IN (1270.0 MM)	WHITE
488-148-524-D	121-810-012	14.0 FT (4.3 M)	50.0 IN (1270.0 MM)	BLACK
488-148-523-D	121-810-002	14.0 FT (4.3 M)	50.0 IN (1270.0 MM)	SILVER SATIN
488-108-522-D	121-810-021	10.0 FT (3.0 M)	42.0 IN (1066.8 MM)	WHITE
488-108-521-D	121-810-011	10.0 FT (3.0 M)	42.0 IN (1066.8 MM)	BLACK
488-108-520-D	121-810-001	10.0 FT (3.0 M)	42.0 IN (1066.8 MM)	SILVER SATIN
488-078-525-D	121-810-020	7.0 FT (2.1 M)	28.0 IN (711.2 MM)	WHITE
488-078-524-D	121-810-010	7.0 FT (2.1 M)	28.0 IN (711.2 MM)	BLACK
488-078-523-D	121-810-000	7.0 FT (2.1 M)	28.0 IN (711.2 MM)	SILVER SATIN
488-058-522-D	121-810-023	5.0 FT (1.5 M)	22.0 IN (558.8 MM)	WHITE
488-058-521-D	121-810-013	5.0 FT (1.5 M)	22.0 IN (558.8 MM)	BLACK
488-058-520-D	121-810-003	5.0 FT (1.5 M)	22.0 IN (558.8 MM)	SILVER SATIN
IOI PART NUMBER	IOI CABLE PART NUMBER	EXTENDED LENGTH "X"	RETRACTED LENGTH "R"	

TABULATION BLOCK

		I/O INTERCONNECT SANTA ANA, CALIFORNIA	
		TITLE: 899C COIL CABLE TO OPEN END, CABLE ASSEMBLY	PART NO.: 488-XXB-52X-D ENG. NO.: 488-XXB-52X-D CUSTOMER: DIGI KEY SCALE: NONE SHEET 1 OF 1
UNLESS OTHERWISE NOTED, DIMENSIONS ARE IN INCHES (MILLIMETERS) TOLERANCES: XXX ± 0.25 (6.35)		DIMENSIONS ARE IN INCHES (MILLIMETERS) TOLERANCES: XXX ± 0.25 (6.35)	
MODULAR COIL CABLE, 26 AWG (7/34) BARE COPPER, 8 CONDUCTOR, UNSHIELDED, PVC JACKET, (SEE TABULATION BLOCK FOR COLOR).		CONNECTOR, MODULAR PLUG, 8 POSITION, 8 CONDUCTOR, 50U" AU, FLAT TYPE EXIT.	
ITEM 1 QTY 1 PC MFG. IOI		DESCRIPTION CABLE ASSEMBLY PARTS LIST	