




LOC		DIST		REVISONS			
F	LTR	DESCRIPTION		DATE	DWN	APVD	
	B	REVISED PER ECO-10-012356		14DEC2010	CJV	EJB	

D




- △ HOUSINGS; POLYESTER, UL 94 V-O RATED, NATURAL
SIGNAL AND SIGNAL GROUND CONTACTS: COPPER ALLOY
UTILITY CONTACTS: PHOSPHOR BRONZE
- △ UTILITY CONTACTS: 0.76um MIN GOLD IN CONTACT AREA,
2.54um MIN TIN ON PCB TAILS, OVER 1.27um MIN NICKEL OVER ALL.
SIGNAL AND SIGNAL GROUND CONTACTS: 0.76um MIN GOLD IN CONTACT AREA,
2.54um MIN TIN ON PCB TAILS, OVER 1.27um MIN NICKEL OVER ALL.
3. ROWS A, C, D, AND F ARE SIGNAL CONTACTS. ROWS B AND E ARE SIGNAL GROUND CONTACTS.
- △ CONNECTOR SIZE CAN ACCOMMODATE INDICATED QUANTITY OF DIFFERENTIAL PAIRS.
- △ DIMENSIONS PER CUSTOMER BOARD LAYOUT.
- △ COMPANY LOGO IN APPROXIMATE AREA SHOWN.

D



C

B



B

232	113.44	106.74	88.90	88.39	72	6367580-9
208	103.28	96.58	78.74	78.23	64	6367580-8
184	93.12	86.42	68.58	68.07	56	6367580-7
160	82.96	76.26	58.42	57.91	48	6367580-6
136	72.80	66.10	48.26	47.75	40	6367580-5
112	62.64	55.94	38.10	37.59	32	6367580-4
88	52.48	45.78	27.94	27.43	24	6367580-3
64	42.32	35.62	17.78	17.27	16	6367580-2
40	32.16	25.46	7.62	7.11	8	6367580-1
N	H DIM	D DIM	B DIM	A OR C DIM	DIFF PAIRS △	PART NUMBER

A

TYPICAL DIMENSIONS TO CENTER OF CONTACT UNLESS OTHERWISE SPECIFIED		DWN WM. VAN SCYOC 27MAR05	Tyco Electronics Harrisburg, PA 17105-3608	
CHK N. REESER 27MAR05		NAME N. REESER 27MAR05	Z-DOK+ HOST BOARD CONNECTOR ASSEMBLY, 8-72 SIGNAL DIFF. PAIR, 2 UTILITY CONTACTS PER SIDE	
APVD N. REESER 27MAR05		PRODUCT SPEC 108-1985	SIZE A11 00779	
APPLICATION SPEC 114-13068		WEIGHT -	RESTRICTED TO B	
MATERIAL △		FINISH △	CUSTOMER DRAWING	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 9 PLC ±.3 1 PLC ±0.3 2 PLC ±0.25 3 PLC ±.3 4 PLC ±.3 ANGLES ±.3	SCALE 4:1 SHEET 1 OF 1 REV B	