




MATERIALS:

Body and Fittings – Stainless Steel

Center Contact – Beryllium Copper

Dielectric – Teflon

Finish: Body and Center Contact – Gold Plated

RATINGS:

Operating Temperature: -65°C (-85°F) to +165°C (+329°F)

Operating Voltage: 335 VRMS

Nominal Impedance: 50 Ohms

Frequency Range: DC to 18 GHz

Connectors meet the interface requirement of MIL-C-39012

ORDERING INFORMATION: Model 4850

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

4850