



Surface-Mount Analog Switches

LCC-20



Part Number	Analog Range (V)	$r_{DS(ON)}$ (Ω)	Switching Time t_{on} (ns)	ABS Max. Supply (V)	Configuration
DG201AAZ/883	± 15	175	600	44	SPST(4X)
DG271AZ/883	± 15	50	65	44	SPST(4X)
DG301AAZ/883	± 15	50	300	44	SPDT(1)
DG303AAZ/883	± 15	50	300	44	SPDT(2)
DG307AAZ/883	± 15	50	250	44	SPDT(2)
DG401AZ/883	± 15	35	150	44	SPST(4)
DG403AZ/883	± 15	35	150	44	SPDT(2)
DG405AZ/883	± 15	35	150	44	DPST(2)
DG411AZ/883	± 15	35	250	44	SPST(4X)
DG412AZ/883	± 15	35	250	44	SPST(4X)
DG413AZ/883	± 15	35	250	44	SPST(4X)
DG441AZ/883	± 15	35	250	44	SPST(4X)
DG442AZ/883	± 15	35	250	44	SPST(4X)
DG508AAZ/883	± 15	400	1500	44	MUX 8 X 1
DG509AAZ/883	± 15	400	1500	44	MUX 4 X 2

PLCC-20



Part Number	Analog Range (V)	$r_{DS(ON)}$ (Ω)	Switching Time t_{on} (ns)	ABS Max. Supply (V)	Configuration
DG540DN	-5 to 8	60	70	19	SPST(4)
DG423DN	± 15	35	250	44	SPDT(2)