

## NEW! Convenience Pack Terminals



These convenience packs are ideal for construction and MRO applications.

- Easy to use – locate and manage terminals with a clear package showing industry color coding
- Convenient storage – accessible smaller packaging is resealable and reusable
- Compatible with Panduit terminal kits – delivers ultimate flexibility for a range of job site applications
- Smaller packaging option provides high quality product at an affordable price

| Part Number      | UPC Codes  | Wire Range  | Stud Size | Description                                  | Pkg. Qty. |
|------------------|------------|-------------|-----------|----------------------------------------------|-----------|
| <b>Terminals</b> |            |             |           |                                              |           |
| PN18-6R-E        | 7498336502 | 22 – 18 AWG | #6        | Ring terminal, nylon insulated               | 20        |
| PN18-8R-E        | 7498336504 | 22 – 18 AWG | #8        | Ring terminal, nylon insulated               | 20        |
| PN18-10R-E       | 7498336499 | 22 – 18 AWG | #10       | Ring terminal, nylon insulated               | 20        |
| PN14-6R-E        | 7498336555 | 16 – 14 AWG | #6        | Ring terminal, nylon insulated               | 20        |
| PN14-8R-E        | 7498336559 | 16 – 14 AWG | #8        | Ring terminal, nylon insulated               | 20        |
| PN14-10R-E       | 7498336552 | 16 – 14 AWG | #10       | Ring terminal, nylon insulated               | 20        |
| PN14-14R-E       | 7498336553 | 16 – 14 AWG | 1/4"      | Ring terminal, nylon insulated               | 20        |
| PN10-8R-E        | 7498336550 | 12 – 10 AWG | #8        | Ring terminal, nylon insulated               | 20        |
| PN10-10R-E       | 7498336545 | 12 – 10 AWG | #10       | Ring terminal, nylon insulated               | 20        |
| PN10-12R-E       | 7498336546 | 12 – 10 AWG | 1/2"      | Ring terminal, nylon insulated               | 20        |
| PN10-14R-E       | 7498336547 | 12 – 10 AWG | 1/4"      | Ring terminal, nylon insulated               | 20        |
| PN10-38R-E       | 7498336548 | 12 – 10 AWG | 3/8"      | Ring terminal, nylon insulated               | 20        |
| PNF14-10R-E      | 7498336505 | 16 – 14 AWG | #10       | Ring terminal, nylon insulated, funnel entry | 20        |
| PN18-6F-E        | 7498336500 | 22 – 18 AWG | #6        | Fork terminal, nylon insulated               | 20        |
| PN18-8F-E        | 7498336503 | 22 – 18 AWG | #8        | Fork terminal, nylon insulated               | 20        |
| PN14-6F-E        | 7498336554 | 16 – 14 AWG | #6        | Fork terminal, nylon insulated               | 20        |
| PN14-8F-E        | 7498336556 | 16 – 14 AWG | #8        | Fork terminal, nylon insulated               | 20        |
| PN14-10F-E       | 7498336551 | 16 – 14 AWG | #10       | Fork terminal, nylon insulated               | 20        |
| PN10-8F-E        | 7498336549 | 12 – 10 AWG | #8        | Fork terminal, nylon insulated               | 20        |
| PN10-10F-E       | 7498336543 | 12 – 10 AWG | #10       | Fork terminal, nylon insulated               | 20        |
| PN18-6LF-E       | 7498336501 | 22 – 18 AWG | #6        | Locking fork terminal, nylon insulated       | 20        |
| PN14-8LF-E       | 7498336558 | 16 – 14 AWG | #8        | Locking fork terminal, nylon insulated       | 20        |
| PN10-10LF-E      | 7498336544 | 12 – 10 AWG | #10       | Locking fork terminal, nylon insulated       | 20        |
| PNF14-8F-E       | 7498336506 | 16 – 14 AWG | #8        | Fork terminal, nylon insulated, funnel entry | 20        |
| PK18-6R-E        | 7498336542 | 22 – 18 AWG | #6        | Ring terminal, KYNAR* insulated              | 20        |
| PK14-8R-E        | 7498336541 | 16 – 14 AWG | #8        | Ring terminal, KYNAR* insulated              | 20        |
| PK14-10R-E       | 7498336540 | 16 – 14 AWG | #10       | Ring terminal, KYNAR* insulated              | 20        |
| PK10-10R-E       | 7498336495 | 12 – 10 AWG | #10       | Ring terminal, KYNAR* insulated              | 20        |
| PV18-6R-E        | 7498336361 | 22 – 18 AWG | #6        | Ring terminal, vinyl insulated               | 20        |
| PV18-8R-E        | 7498336363 | 22 – 18 AWG | #8        | Ring terminal, vinyl insulated               | 20        |
| PV18-10R-E       | 7498336359 | 22 – 18 AWG | #10       | Ring terminal, vinyl insulated               | 20        |
| PV18-14R-E       | 7498336364 | 22 – 18 AWG | 1/4"      | Ring terminal, vinyl insulated               | 20        |
| PV14-6R-E        | 7498336255 | 16 – 14 AWG | #6        | Ring terminal, vinyl insulated               | 20        |
| PV14-8R-E        | 7498336357 | 16 – 14 AWG | #8        | Ring terminal, vinyl insulated               | 20        |
| PV14-10R-E       | 7498336244 | 16 – 14 AWG | #10       | Ring terminal, vinyl insulated               | 20        |
| PV14-14R-E       | 7498336377 | 16 – 14 AWG | 1/4"      | Ring terminal, vinyl insulated               | 20        |
| PV14-10RX-E      | 7498336376 | 16 – 14 AWG | #10       | Ring terminal, vinyl expanded insulation     | 20        |
| PV10-6R-E        | 7498336691 | 12 – 10 AWG | #6        | Ring terminal, vinyl insulated               | 20        |
| PV10-8R-E        | 7498336243 | 12 – 10 AWG | #8        | Ring terminal, vinyl insulated               | 20        |
| PV10-10R-E       | 7498336239 | 12 – 10 AWG | #10       | Ring terminal, vinyl insulated               | 20        |
| PV10-14R-E       | 7498336241 | 12 – 10 AWG | 1/4"      | Ring terminal, vinyl insulated               | 20        |
| PV10-56R-E       | 7498336426 | 12 – 10 AWG | 5/16"     | Ring terminal, vinyl insulated               | 20        |
| PV10-38R-E       | 7498336425 | 12 – 10 AWG | 3/8"      | Ring terminal, vinyl insulated               | 20        |
| PV18-6F-E        | 7498336360 | 22 – 18 AWG | #6        | Fork terminal, vinyl insulated               | 20        |
| PV18-6LF-E       | 7498336365 | 22 – 18 AWG | #6        | Locking fork terminal, vinyl insulated       | 20        |
| PV18-8F-E        | 7498336362 | 22 – 18 AWG | #8        | Fork terminal, vinyl insulated               | 20        |
| PV18-8LF-E       | 7498336366 | 22 – 18 AWG | #8        | Locking fork terminal, vinyl insulated       | 20        |
| PV18-10F-E       | 7498336358 | 22 – 18 AWG | #10       | Fork terminal, vinyl insulated               | 20        |

Unified Physical Infrastructure



building a smarter, unified business foundation  
Connect. Manage. Automate.

**PANDUIT®**

| Part Number          | UPC Codes  | Wire Range  | Stud Size | Description                                    | Pkg. Qty. |
|----------------------|------------|-------------|-----------|------------------------------------------------|-----------|
| <b>Terminals</b>     |            |             |           |                                                |           |
| PV14-6F-E            | 7498336254 | 16 – 14 AWG | #6        | Fork terminal, vinyl insulated                 | 20        |
| PV14-6LF-E           | 7498336378 | 16 – 14 AWG | #6        | Locking fork terminal, vinyl insulated         | 20        |
| PV14-8F-E            | 7498336348 | 16 – 14 AWG | #8        | Fork terminal, vinyl insulated                 | 20        |
| PV14-8LF-E           | 7498336422 | 16 – 14 AWG | #8        | Locking fork terminal, vinyl insulated         | 20        |
| PV14-10F-E           | 7498336374 | 16 – 14 AWG | #10       | Fork terminal, vinyl insulated                 | 20        |
| PV14-10LF-E          | 7498336375 | 16 – 14 AWG | #10       | Locking fork terminal, vinyl insulated         | 20        |
| PV10-6F-E            | 7498336427 | 12 – 10 AWG | #6        | Fork terminal, vinyl insulated                 | 20        |
| PV10-8F-E            | 7498336242 | 12 – 10 AWG | #8        | Fork terminal, vinyl insulated                 | 20        |
| PV10-8LF-E           | 7498336428 | 12 – 10 AWG | #8        | Locking fork terminal, vinyl insulated         | 20        |
| PV10-10F-E           | 7498334424 | 12 – 10 AWG | #10       | Fork terminal, vinyl insulated                 | 20        |
| PV10-10LF-E          | 7498336424 | 12 – 10 AWG | #10       | Locking fork terminal, vinyl insulated         | 20        |
| PV10-14F-E           | 7498336240 | 12 – 10 AWG | 1/4"      | Fork terminal, vinyl insulated                 | 20        |
| P14-10R-E            | 7498336539 | 16 – 14 AWG | #10       | Ring terminal, non-insulated                   | 20        |
| P14-14R-E            | 7498336689 | 16 – 14 AWG | 1/4"      | Ring terminal, non-insulated                   | 20        |
| P10-10R-E            | 7498336492 | 12 – 10 AWG | #10       | Ring terminal, non-insulated                   | 20        |
| P10-10RHT6-E         | 7498336493 | 12 – 10 AWG | #10       | Ring terminal, non-insulated, high temperature | 20        |
| P10-14R-E            | 7498336494 | 12 – 10 AWG | 1/4"      | Ring terminal, non-insulated                   | 20        |
| P14-8F-E             | 7498336690 | 16 – 14 AWG | #8        | Fork terminal, non-insulated                   | 20        |
| <b>Pin Terminals</b> |            |             |           |                                                |           |
| PV18-P47-E           | 7498336367 | 22 – 18 AWG | —         | Pin terminal, vinyl insulated                  | 20        |
| PV14-P47-E           | 7498336423 | 16 – 14 AWG | —         | Pin terminal, vinyl insulated                  | 20        |
| PV10-P55-E           | 7498336429 | 12 – 10 AWG | —         | Pin terminal, vinyl insulated                  | 20        |
| <b>Disconnects</b>   |            |             |           |                                                |           |
| DNF18-110FIB-E       | 7498336439 | 22 – 18 AWG | —         | Female disconnect, nylon F.I.                  | 20        |
| DNF18-111FIB-E       | 7498336440 | 22 – 18 AWG | —         | Female disconnect, nylon F.I.                  | 20        |
| DNF18-250FIB-E       | 7498334196 | 22 – 18 AWG | —         | Female disconnect, nylon F.I.                  | 20        |
| DNF14-188FIB-E       | 7498336435 | 16 – 14 AWG | —         | Female disconnect, nylon F.I.                  | 20        |
| DNF14-250FIB-E       | 7498334192 | 16 – 14 AWG | —         | Female disconnect, nylon F.I.                  | 20        |
| DNF10-250FIB-E       | 7498336432 | 12 – 10 AWG | —         | Female disconnect, nylon F.I.                  | 20        |
| DNF10-250FI-E        | 7498334190 | 12 – 10 AWG | —         | Female disconnect, nylon F.I.                  | 20        |
| DNF10-250FIMB-E      | 7498336433 | 12 – 10 AWG | —         | Male disconnect, nylon F.I.                    | 20        |
| DNF18-110-E          | 7498336438 | 22 – 18 AWG | —         | Female disconnect, nylon barrel insulated      | 20        |
| DNF18-250-E          | 7498336441 | 22 – 18 AWG | —         | Female disconnect, nylon barrel insulated      | 20        |
| DNF14-110-E          | 7498336434 | 16 – 14 AWG | —         | Female disconnect, nylon barrel insulated      | 20        |
| DNF14-250-E          | 7498336436 | 16 – 14 AWG | —         | Female disconnect, nylon barrel insulated      | 20        |
| DNF18-250FIM-E       | 7498334298 | 22 – 18 AWG | —         | Male disconnect, nylon F.I.                    | 20        |
| DNF14-250FIM-E       | 7498334193 | 16 – 14 AWG | —         | Male disconnect, nylon F.I.                    | 20        |
| DNF14-250M-E         | 7498336437 | 16 – 14 AWG | —         | Male disconnect, nylon barrel insulated        | 20        |
| DNFR18-250FIB-E      | 7498336443 | 22 – 18 AWG | —         | Female disconnect, right angle, nylon F.I.     | 20        |
| DNFR14-250FIB-E      | 7498336442 | 16 – 14 AWG | —         | Female disconnect, right angle, nylon F.I.     | 20        |
| DV18-250B-E          | 7498336490 | 22 – 18 AWG | —         | Female disconnect, vinyl barrel insulated      | 20        |
| DV14-250B-E          | 7498334355 | 16 – 14 AWG | —         | Female disconnect, vinyl barrel insulated      | 20        |
| DV14-250MB-E         | 7498336444 | 16 – 14 AWG | —         | Male disconnect, vinyl barrel insulated        | 20        |
| DV10-250-E           | 7498334354 | 12 – 10 AWG | —         | Female disconnect, vinyl barrel insulated      | 20        |
| DV18-250P-E          | 7498336491 | 22 – 18 AWG | —         | Piggyback disconnect, vinyl barrel insulated   | 20        |
| DV14-250P-E          | 7498336489 | 16 – 14 AWG | —         | Piggyback disconnect, vinyl barrel insulated   | 20        |
| <b>Butt Splices</b>  |            |             |           |                                                |           |
| BS14-E               | 7498336430 | 16 – 14 AWG | —         | Butt splice, non-insulated                     | 20        |
| BS10-E               | 7498336431 | 12 – 10 AWG | —         | Butt splice, non-insulated                     | 20        |
| BSN18-E              | 7498334185 | 22 – 18 AWG | —         | Butt splice, nylon insulated                   | 20        |
| BSN14-E              | 7498329325 | 16 – 14 AWG | —         | Butt splice, nylon insulated                   | 20        |
| BSN10-E              | 7498329299 | 12 – 10 AWG | —         | Butt splice, nylon insulated                   | 20        |
| BSV18X-E             | 7498334189 | 22 – 18 AWG | —         | Butt splice, vinyl insulated                   | 20        |
| BSV14X-E             | 7498334188 | 16 – 14 AWG | —         | Butt splice, vinyl insulated                   | 20        |
| BSV10X-E             | 7498334186 | 12 – 10 AWG | —         | Butt splice, vinyl insulated                   | 20        |

#### WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA  
Markham, Ontario  
cs-cdn@panduit.com  
Phone: 800.777.3300

PANDUIT EUROPE LTD.  
London, UK  
cs-emea@panduit.com  
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.  
Republic of Singapore  
cs-ap@panduit.com  
Phone: 65.6305.7575

PANDUIT JAPAN  
Tokyo, Japan  
cs-japan@panduit.com  
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA  
Jalisco, Mexico  
cs-la@panduit.com  
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.  
Victoria, Australia  
cs-aus@panduit.com  
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to [www.panduit.com/warranty](http://www.panduit.com/warranty)

For more information

Visit us at [www.panduit.com](http://www.panduit.com)

Contact Customer Service by email: [cs@panduit.com](mailto:cs@panduit.com)  
or by phone: 800-777-3300 and reference TMFL05

© 2009 Panduit Corp.  
ALL RIGHTS RESERVED.  
Printed in the U.S.A.

WW-TMFL05

9/2009

**PANDUIT®**