



Sample photo

Order symbol: ABS 95/35 LG
Product nbr: 6082331
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074054692
El. number:
Finland: 3421376
Denmark: 8212023929
Sweden: 6082331
Norway:

Including: Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		100	100	35	Ingress Protection (EN 60529): IP 66/67
inch:		3.9	3.9	1.4	Impact Resistance (EN 62262): IK 07
Materials:					Electrical insulation: Totally insulated
Material:		ABS			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			Flammability Rating (UL 746 C 5): UL 94 HB
Cover colour:		RAL 7035			Glow Wire Test (IEC 695-2-1) °C: 650
Cover screws material:		Polyamide			NEMA Class: NEMA 1, 4, 4X, 6, 12, 13
Cover screws colour:		Grey			
Gasket material:		Polyurethane			
Temperatures:					Certificates:
Short term:		-40 ... 80 °C			Fimko
Continuous:		-40 ... 60 °C			Europe EN 62208: 2003
Short term:		-40 ... 175 °F			Gost R
Continuous:		-40 ... 140 °F			
Accessories:					
MIV 95		Mounting plate (Galvanized steel)			
MIN 8		DIN-15 Mounting rail			
B-3		DIN-35 Mounting rail			
FP 22046		Wall fastening lug (4 pcs)			

