

HARDWARE SPECIFICATION		
1	LAN PORT	Ethernet: 2x RJ-45, 10/100BASE-TX
2	SERIAL PORT	1x RS-232/422/485, 9 POS. MALE D-SUB RS-232 SIGNALS: TXD, RXD, RTS, CTS, DTR, DSR, DCD, GND SERIAL LINE PROTECTION: 15kV ESD FOR ALL SIGNALS
3	SERIAL COMMUNICATION PARAMETERS	SPEED: 110bps to 460.8kbps FLOW CONTROL: RTS/CTS, XON/XOFF DATA BITS: 5, 6, 7, 8 STOP BITS: 1, 1.5, 2 PARITY: NONE, EVEN, ODD, SPACE, MARK
4	BEEPER	BEEPER FOR ACOUSTIC EVENT WARNING
5	LED	PWR1: POWER 1 AND SYSTEM STATUS PWR2: POWER 2 AND SYSTEM STATUS Eth1 and Eth2 LNK/ACT: LAN PORT STATUS TX/RX: SERIAL PORT TRANSMISSION STATUS
6	POWER SUPPLY	WIDE RANGE REDUNDANT SUPPLY: 12 TO 48 V DC REVERSE POLARITY PROTECTION POWER LINE BURST PROTECTION 1kV (EN61000-4-4, PRODUCT SPEC. TEST 2.3) POWER LINE SURGE PROTECTION 0.5kV (EN61000-4-5, PRODUCT SPEC. TEST 2.4)
7	POWER CONSUMPTION	3.55 WATTS

[illegible]