




THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.  
© 2003, Projects Unlimited Inc.

## SPECIFICATIONS

PARAMETERS	VALUES	UNITS
RATED VOLTAGE	12	Vdc
OPERATING VOLTAGE RANGE	6 ~ 28	Vdc/Vac
RATED CURRENT (MAX)	10	mA
MINIMUM SPL @ 10 cm.	90	dB
RESONANT FREQUENCY	2,800±500	Hz
TONE OR PULSE RATE	SLOW	1.2 PULSE PER SECOND
OPERATING TEMPERATURE	-30 ~ +85	°C
STORAGE TEMPERATURE	-40 ~ +85	°C
HOUSING MATERIAL	NYLON UL-94-V-0	-
TERMINAL MATERIAL	TIN-PLATED TAPPED SCREW	-
WEIGHT	33.8	grams

## REVISIONS

LTR	DESCRIPTION	DATE	APPROVED
-	RELEASED FROM ENGINEERING	2/25/04	
A	REVISED TERMINAL MATERIAL	8/16/04	R. W.
B	ADDED IP RATING	04/14/05	E. P.



### NOTES:

- ALL DIMENSIONS ARE IN MILLIMETERS.
- SPECIFICATION SUBJECT TO CHANGE OR WITHDRAWAL WITHOUT NOTICE.
- THIS PART IS IP67 RATED.

UNLESS OTHERWISE SPECIFIED:  
DIMENSIONS ARE IN  
MILLIMETERS, TOLERANCES ARE ±0.5 AND  
ANGLES ARE ±3°.

APPROVALS DATE  
DRAWN R. A. C. 2/04

APPROVED R. W. 2/04

DO NOT SCALE DRAWING



projects®  
unlimited

Dayton, Ohio

PIEZO AUDIO INDICATOR  
AI-4228-P-SP28D

SIZE A DRAWING NO.  
AI-4228-P-SP28D

SCALE: N.T.S.

SHEET 1 OF 1

THIS PART IS UL RECOGNIZED  
IN THE USA AND CANADA.

FILE NAME

AI-4228-P-SP28D.DWG

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[AI-4228-P-SP28D](#)