



LOC		DIST		REV		DATE		APPRO	
G	14	P	F	ZONE	LTR	DESCRIPTION	DATE	APPRO	
				C		REV 8 REDRAWN PER 0720-0040-93	3-26-93	YB DAP	

METRIC
DIMENSIONS LISTED IN mm [INCHES]

AMP WIRE RANGE	UL E13288 Listed
16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED
UL LR7189 Certified	MILITARY P/N AND CLASS
16-14 AWG SOLID OR STRANDED	NOT APPLICABLE

△ STAMP AMP 16-14* APPROX AS SHOWN



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 1.04-2.62mm² [2,050-5,180] CIR MILS SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE ADVISED FOR THE LATEST REVISION.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 3 PLC DEC ± ANGLES		DR 3-26-93 TA BRINKMAN	NAME AMP AMP Incorporated Harrisburg, PA 17105-3608
MATERIAL COPPER PER ASTM B-152 ANNEALED		CHK 3-26-93 DA PATTERSON	
FINISH TIN PLATE 0.00254 [0.00100] MIN THK PER MIL-T-10727		APPD 3-26-93 DE MILLER	
APPLICATION SPEC		APPD 3-26-93 JL MECKLEY	
SIZE CAGE CODE 00779	DRAWING NO C=320815	SCALE 10:1	

TERMINAL, RECTANGULAR
TONGUE, SOLISTRAND™

PART NO
320815

320815