


ENERGIZER NO. 411



Industry Standard Dimensions in mm (inches)



Chemical System: Zinc-Manganese Dioxide (Zn/MnO₂)

Designation: ANSI / NEDA-208, IEC-10F20

Battery Voltage: 15 Volts

Average Weight: 27 grams (1.0 oz.)

Volume: 15 cubic centimeters (0.9 cubic inch)


Average Capacity: 140 mAh to 0.8 volts/cell
 (Rated at 25 mA continuous drain at 21°C)

Cells: Ten No. 112 in series

Jacket: Metal

TYPICAL DISCHARGE CURVE

Simulated Test @ 21°C (70°F)



Simulated Application Test **Estimated Average Service at 21°C (70°F)**

Schedule:	Typical Drains at 12V (milliamperes)	Load (ohms)	Cutoff Voltage					
			8.0V	9.0V	10V	11V	12V	13V
			Hours					
4 hours/day	0.8	15,000	209	197	184	167	134	55

Important Notice

This data sheet contains information specific to batteries manufactured at the time of its publication.

Contents herein do not constitute a warranty.

Copyright © Eveready Battery Co. Inc. - All Rights Reserved

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Energizer:](#)

[411](#)