




Dimensions: mm (In.)



Mouser Stock No.	Button Color	Frame Color	Circuit
107-1258-S	Silver	Black	Off-On
107-1258R	Red	Black	Off-On
107-1258B	Black	Black	Off-On
107-1258BU	Blue	Black	Off-On
107-1259-B	Black	Black	Off-(On)
107-1259-R	Red	Black	Off-(On)
107-1259-S	Silver	Black	Off-(On)
107-1259BU	Blue	Black	Off-(On)



Electrical Specifications:

- Rating: 3A/125VAC
- Insulation resistance: 100M Ω 500VDC
- Contact resistance: 20m Ω @ 2.5VDC 1A
- Dielectric Strength: 1000V for 1 minute

Mechanical Specifications:

- Type: SPST

Mouser Stock No.	Button Color	Frame Color	Circuit
107-1261B	Black	Black	Off-On
107-1261R	Red	Black	Off-On
107-1262-R	Red	Black	Off-(On)
107-1262-B	Black	Black	Off-(On)
107-1262C	Cream	Black	Off-(On)
107-2261R	Red	Gray	Off-On
107-2262-R	Red	Gray	Off-(On)
107-2262-G	Gray	Gray	Off-(On)

Guarded Pushbutton Switches

107-1258 Series 107-1262 Series
 107-1259 Series 107-2261 Series
 107-1261 Series 107-2262 Series

Mountain
Switch

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mountain Switch:

[107-2259-R](#) [107-2259-S](#) [107-1259BU](#) [107-1262C](#) [107-1261C](#) [107-1261G](#) [107-2261R](#) [107-2262-R](#) [107-2262-G](#)
[107-1258B](#)

Other:

[107-2261G](#) [107-2261C](#)