




REV.	DATE	ECR NO.	DESCRIPTION
NC	01/19/98	—	INITIAL RELEASE
A	06/24/08	100039	UPDATE DRAWING FORMAT



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”	APPROVALS		DATE		Amphenol Connex						
8						DRAWN	GRS	06/24/08								
7						CHECKED				PART DESCRIPTION MCX DIRECT SOLDER JACK (FOR .085”, .086” CABLE)						
6						ISSUED										
5					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”	SHEET	1 OF 1				PART NO. 252131					
4																
3	CONTACT PIN	BER. COPPER	GOLD	1						DWG. NO. 252131.DWG						
2	INSULATOR	PTFE	NATURAL	1												
1	BODY	BRASS	GOLD	1							REV. A		SIZE A	SCALE NA		
DESCRIPTION					MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING		C:/252/252131.DWG						