

Power It! Power Strip with 4 Outlets and 10-ft. Cord

MODEL NUMBER: **PS410**



Description

Tripp Lite's Power It! PS410 power strip offers reliable, convenient and cost-effective power distribution for appliances, power tools, lighting and other electrical equipment. Includes 4 NEMA 5-15R outlets, 10-foot AC power cord.. Multi-outlet strip reduces cable clutter and enables the connection of multiple electrical devices to a single AC wall socket. Features ABS fire retardant plastic case to stand up to the most demanding environments, illuminated power switch and 15A integrated circuit breaker to prevent dangerous overloads.

INPUT/OUTPUT: Input: NEMA 5-15P/Output: 4 NEMA 5-15R

ELECTRICAL: 120V AC, 50/60Hz, 15A

FORMAT: Corded power distribution strip

Features

- Multi-outlet power strip offers reliable, convenient and cost-effective power distribution for appliances, power tools, lighting and other electrical equipment
- Includes 4 NEMA 5-15R outlets
- Illuminated on/off switch provides one-touch power control for connected equipment
- 15A power handling capacity with integrated circuit breaker
- 120V AC, 50/60Hz electrical compatibility
- 10-foot AC power cord
- ABS fire retardant plastic case provides extra safety and durability
- UL certification

Specifications

General Info	
Product Group	POWER STRIPS
OVERVIEW	

Highlights

- 4 outlets
- Illuminated on/off switch with cover
- 15-amp circuit breaker
- 10 ft. power cord
- ABS fire retardant plastic

Applications

- Offers a reliable, convenient and cost-effective method of power distribution for appliances, power tools, lighting and other electrical equipment in home, office or worksite.
- Unfiltered electrical pass-through makes the power strip ideal for distributing alternate waveform UPS or generator power to connected equipment.

Package Includes

- PS410 power strip
- Warranty information
- Instruction manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Intended Application	Home/Office; Industrial/Factory Floor
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Circuit Breaker (amps)	15
Overload Protection	15A circuit breaker
Outlet Quantity / Type	4 NEMA 5-15R
Outlet Orientation	Single row of 4
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Connection Type	NEMA 5-15P
Input Cord Length (ft.)	10
Input Cord Length (m)	1.8
Input Cord Gauge Type	SJT 14AWG
Voltage Compatibility (VAC)	120
LEDS ALARMS & SWITCHES	
Switches	Illuminated on/off switch controls power to all outlets
PHYSICAL	
Shipping Dimensions (hwd / in.)	12 x 5.8 x 1.8
Shipping Dimensions (hwd / cm)	30.5 x 14.7 x 4.6
Shipping Weight (lbs.)	1.2
Shipping Weight (kg)	.544
Unit Dimensions (hwd / in.)	1.2 x 1.85 x 8.1
Unit Dimensions (hwd / cm)	3 x 4.7 x 20.6
Unit Weight (lbs.)	1.4
Unit Weight (kg)	.6
Material of Construction	ABS Fire Retardant Plastic
Integrated Keyhole Mounting Tabs	Keyhole Slots
Receptacle Color	Light Gray
Color (AC Line Cord)	Light Gray
Style	Strip



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

CERTIFICATIONS	
Additional International Approvals	Complies with RoHS (Restriction of Hazardous Substances Directive)
UL1363 (Power Tap)	UL1363
cUL / CSA (Canada)	cUL
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.