


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200800313](#)
Status: **Active**
Overview: [Brad Ultra-Lock Connection System](#)
Description: Micro-Change (M12) to Ultra-Lock (M12) Double-Ended Cordset, 5 Poles, Female (Straight) to Male (Straight), 22 AWG, PVC Cable, 2.0m (6.56') Length



Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	LR6837
General	
Product Family	Industrial Cordsets
Series	120080
Connector End A	Micro-Change (M12)
Connector End B	Ultra-Lock (M12)
IP Rating	IP69K
Material - Contact	Copper Alloy
Overview	Brad Ultra-Lock Connection System
Product Name	Micro-Change (M12), Ultra-Lock (M12)
Protocol	PROFINET
Region	America
Type	Double Ended
UPC	78678884930
Physical	
Cable Diameter	5.72mm (.225")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Yellow
Coupling Style	Push to Lock
Gender	Female-Male
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	PUR
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Orientation	Straight to Straight
Poles	5
Temperature Range - Operating	-25°C to +90°C
Wire Size AWG	22
Wire/Cable Type	UL 2661
Electrical	
Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC
Material Info	
Engineering Number	WW5030A09M020
Reference - Drawing Numbers	
Sales Drawing	SD-120080-001

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[120080](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION