


INTERCONNECTION

Single Row Receptacle and Plug Housings

Receptacles

TYPE NO.	POLES	A	B
CTHF/MICRO/2/S	2	3.00	6.85
CTHF/MICRO/3/S	3	6.00	9.85
CTHF/MICRO/4/S	4	9.00	12.85
CTHF/MICRO/5/S	5	12.00	15.85
CTHF/MICRO/6/S	6	15.00	18.85


CTHF/MICRO/S



Plugs

TYPE NO.	POLES	A	B
CTHM/MICRO/2/S	2	3.00	6.85
CTHM/MICRO/3/S	3	6.00	9.85
CTHM/MICRO/4/S	4	9.00	12.85
CTHM/MICRO/5/S	5	12.00	15.85
CTHM/MICRO/6/S	6	15.00	18.85


CTHM/MICRO/S



Double Row Headers, Through-Hole, Straight

TYPE NO.	POLES	A	B
CTMV/MICRO/2	2 x 1	-	6.65
CTMV/MICRO/4	2 x 2	3.00	9.65
CTMV/MICRO/6	2 x 3	6.00	12.65
CTMV/MICRO/8	2 x 4	9.00	15.65
CTMV/MICRO/10	2 x 5	12.00	18.65
CTMV/MICRO/12	2 x 6	15.00	21.65
CTMV/MICRO/14	2 x 7	18.00	24.65
CTMV/MICRO/16	2 x 8	21.00	27.65
CTMV/MICRO/18	2 x 9	24.00	30.65
CTMV/MICRO/20	2 x 10	27.00	33.65
CTMV/MICRO/22	2 x 11	30.00	36.65
CTMV/MICRO/24	2 x 12	33.00	39.65

CTMV/MICRO



Double Row Headers, Through-Hole, Right Angle

TYPE NO.	POLES	A	B
CTMH/MICRO/2	2 x 1	-	6.65
CTMH/MICRO/4	2 x 2	3.00	9.65
CTMH/MICRO/6	2 x 3	6.00	12.65
CTMH/MICRO/8	2 x 4	9.00	15.65
CTMH/MICRO/10	2 x 5	12.00	18.65
CTMH/MICRO/12	2 x 6	15.00	21.65
CTMH/MICRO/14	2 x 7	18.00	24.65
CTMH/MICRO/16	2 x 8	21.00	27.65
CTMH/MICRO/18	2 x 9	24.00	30.65
CTMH/MICRO/20	2 x 10	27.00	33.65
CTMH/MICRO/22	2 x 11	30.00	36.65
CTMH/MICRO/24	2 x 12	33.00	39.65

CTMH/MICRO

