

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

94090-4030

Status:

Active

Overview:

Quick-Disconnect Terminals

Description:

Quick Disconnect, 1 Cut, Cover for female terminal, for (0.50-2.50mm²) 14-20 AWG Wire, Accepts 6.35 x 0.81mm Tab




image - Reference only

Series

Documents:

- [Drawing \(PDF\)](#)
- [RoHS Certificate of Compliance \(PDF\)](#)
- [Product Specification PS-94090-001 \(PDF\)](#)

General

Product Family	Quick Disconnects
Series	94090
Crimp Quality Equipment	Yes
Insulated	Fully
Overview	Quick-Disconnect Terminals
Product Name	N/A
Type	Quick Disconnect
UPC	800754327848

Physical

Barrel Type	N/A
Breakaway	No
Circuits (maximum)	1
Color - Resin	Natural
Gender	Female
Glow-Wire Compliant	No
Insulation	None
Lock to Mating Part	None
Material - Resin	Nylon
Net Weight	0.480/g
Number of Rows	1
Orientation	Straight
Packaging Type	Bag
Polarized to Mating Part	Yes
Tab Thickness	N/A
Tab Width	N/A
Temperature Range - Operating	-40°C to +105°C
Wire Insulation Diameter	2.00-4.30mm
Wire Size AWG	14, 16, 18, 20
Wire Size mm²	0.50-2.50

Electrical

Voltage - Maximum	250V
-------------------	------

Material Info

Reference - Drawing Numbers

Product Specification	PS-94090-001
Sales Drawing	SD-94090-020

EU RoHS

ELV and RoHS
Compliant

REACH SVHC

Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product
environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

94090Series

Use With

94030-50**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

94090-4030