

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:


55454-1970

Status:

Active

Description:

1.25mm Pitch Mi II™ System Wire-to-Board Header, Single Row, Right Angle, Lead-Free, 19 Circuits



Documents:	
3D Model	Product Specification PS-54596-018 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	PCB Headers
Series	55454
Application	Signal, Wire-to-Board
Product Name	Mini Mi II™
UPC	756054761120
Physical	
Breakaway	No
Circuits (Loaded)	19
Circuits (maximum)	19
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	804.300/mg
Number of Rows	1
Orientation	Right Angle
PC Tail Length	3.00mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	1.25mm
Polarized to Mating Part	Yes
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	1.5A
Voltage - Maximum	100V
Material Info	
Reference - Drawing Numbers	
Product Specification	PS-54596-018, RPS-54596-024, RPS-54596-027
Sales Drawing	SD-55454-007

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

55454Series

Mates With

51336 PBT Polyester, Glass-filled Housing,

54596 PA Polyamide Housing

This document was generated on 10/14/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION