


Crocodile clips

MA 1



Product	MA 1
description	Miniature alligator clip with high strength insulation and nickel-plated brass/bronze jaws. The part of the jaws (fine wire section) allows a secure contact to be made when clamping even the thinner wire. Capable of clamping flat components (soldering eyes) and wire up to a maximum diameter of 4mm.
operating instruction	BA210
article-no. / *colour	9303178xx  00 black  01 red  02 blue  03 yellow  04 green  06 gray  07 white Ni
drawing	
	
technical data	
connection	2 mm socket
rated voltage ⁽¹⁾	30 VAC / 60 VDC
measurement cat. acc. to IEC 61010	O ⁽³⁾
rated current ⁽¹⁾ (consider derating curve)	8 A
material socket	bronze, nickel plated
housing material	PP
temperature range acc. To IEC61010 ⁽²⁾	-25 °C to +100 °C
flammability class acc. to UL 94 (only valid for basic material of housing)	HB
clamping range	4 mm
standard	IEC 61010

2 mm system

⁽¹⁾ for normal environmental conditions -5°C to +40°C

⁽²⁾ contact the manufacturer for applications at deviating temperature ranges

⁽³⁾ without rated measurement category, for other circuits that are not directly connected to mains

stand: 12.07.2019