



NOTES:

1. ALL DIMENSION IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. CONTACT RATING SWITCHING: 150mA, 250V AC/DC
350mA, 110V AC/DC
5. OPERATING FORCE: 425±100 CM/STANDARD
6. OPERATING TEMP: -30° to 85°C
7. CIRCUIT SP: 12 POSITIONS, 30° INDEX, NO STOPS
8. DIELECTRIC STRENGTH: 1000V RMS min.@Sea Level
9. ▲ DESIGNATE MAJOR FEATURE
- ▲ 10. HARDWARE SUPPLIED ON SWITCH— SEE BELOW
LOCKWASHER, & HEX NUT





CONTACT CONFIGURATION

Timing: **SHORTING**



TERMINATION DETAIL

SCALE 2X



				TITLE			
				KC-10-A-(9.5mm) 01-S-L-S			
A	12822	RELEASED FOR PRODUCTION	2/18/03	CJB			
REV.	ECN No.	DESCRIPTION	DATE	CHKD			
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED							
SCALE				1.5:1	DATE	2/18/03	DR
					CJB	DWG	G527524
						REV	A