



**Features**

- ✓ Available from Stock in Convenient 5-Packs
- ✓ PFA or Glass Braid Insulation
- ✓ 20, 24, 30 and 36 AWG Wires
- ✓ Made from Special Limits of Error Wire
- ✓ 36 and 72 inch Lengths Standard
- ✓ NIST Calibration Available


| Model No.          | AWG Gage | Dia.   | Insulation  |
|--------------------|----------|--------|-------------|
| 5TC-GG-(*)-20-(**) | 20       | 0.032" | Glass Braid |
| 5TC-GG-(*)-24-(**) | 24       | 0.020" | Glass Braid |
| 5TC-GG-(*)-30-(**) | 30       | 0.010" | Glass Braid |
| 5TC-TT-(*)-20-(**) | 20       | 0.032" | PFA         |
| 5TC-TT-(*)-24-(**) | 24       | 0.020" | PFA         |
| 5TC-TT-(*)-30-(**) | 30       | 0.010" | PFA         |
| 5TC-TT-(*)-36-(**) | 36       | 0.005" | PFA         |

\*Specify calibration: J, K, T or E

\*\*Specify length: 36 or 72 inches

| Calibrations    |                    |                   |                      |
|-----------------|--------------------|-------------------|----------------------|
| J =             | K =                | T =               | E =                  |
| Iron-Constantan | CHROMEGA®-ALOMEGA® | Copper-Constantan | CHROMEGA®-Constantan |

**PFA insulation**



**Glass Braid insulation**

