

Feature -

DPDT
on-on function


Application -

consumer products
computer products
instrumentation
communication equipments

► **SPECIFICATIONS**


SWITCH SPECIFICATIONS	
POLE - POSITION	1P2T , Momentary
CONTACT RATING	36 V DC , 0.2 A
CONTACT RESISTANCE	40 mΩ MAX. 1.5 V DC ; 100 mA , by Method of Voltage DROP
INSULATION RESISTANCE	100 MΩ MIN. 500 V DC
DIELECTRIC STRENGTH	Breakdown is not Allowable 500 V DC for 1 Minute
OPERATING FORCE	300 ± 100gf
OPERATING LIFE	1,000,000 cycles
OPERATING TEMPERATURE RANGE	-20°C ~ 70°C
TOTAL TRAVEL	5.8 ± 0.3 mm

► **HOW TO ORDER**





► DIMENSION


PS022-N12AXX



PS022-N12AAW



► CIRCUIT



► P.C.B LAYOUT



► MATERIAL

- COVER : PA + GF
- ACTUATOR : PA + GF
- BASE FRAME : PA + GF
- CAP : PA
- TERMINAL : BRONZE GOLD FLASH

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Well Buying:](#)

[PS022-N12AAW](#)