

H.K. Porter
Light Duty, Clipper Cut Pneumatic Cutter



◀◀ previous print close next ▶▶

Product Details	
Catalog No.	9190NE
UPC Code	037103924513
Weight	11 lbs.
Jaw Design /Cutting Blade	Jaw /Clipper Cut
Replacement Cutterhead /Jaws	9113NE, 9112NE
Material Type	Rod
Capacity	See Tech Specs Link Below
Operating Pressure /CFM	80-120 psi 6.9 - 8 CFM
Bore and Stroke	4 in./ 2 in.
Packaging	Industrial Box /Carton
Literature	Safety-Tool Select-Cuttime.pdf
Tech. Spec.	9190C Specifications.pdf
Low Res. Image	9190NE 100.jpg
High Res. Image	9190NE 300.jpg
Parts List	Parts for 9190NE.pdf
Stock Item	Normal Stock Item

Package Details (Dimensions)

Email this Page

Product Features:

- Lightweight model for 80-120 psi
- Used in the wire-shelving industry
- No exhaust shock
- Clipper cut jaws
- Cuts soft, or medium materials
- Light duty workhead has 4" bore (102mm) and 2" stroke (51mm)

- **Cutting controlled by manual pressure**
- **Filter-lubricator units recommended in air supply line-long tool service**
- **NEVER use any H.K. Porter cutters on energized circuits, wire, or cable!**