



Dimensions: mm (in.)

**Electrical Specifications:**

- Rating: Non-switching: 100mA/50V DC
Switching: 25mA/24V DC
- Contact resistance: 100mΩ max. (initial)
- Insulation resistance: 100MΩ min.

Note:

- RoHS Compliant and Process Compatible with 260° solder

Mechanical Specifications:

- Operating temperature: -40°C ~ +85°C
- Operation force: 500gf max.

Mouser Stock No.	No. of Pos.	Dim A. mm (In.)	Top Tape
106-HN2-EV	2	3.77 (.148)	Without
106-HN4-EV	4	6.31 (.248)	Without
106-HN6-EV	6	8.85 (.348)	With
106-HN8-EV	8	11.39 (.448)	With
106-HN1-EV	10	13.93 (.548)	With

Dip Switches

106-HN2-EV, 106-HN4-EV, 106-HN6-EV,
106-HN8-EV, 106-HN1-EV

**Mountain
Switch**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mountain Switch:

[106-HN2-EV](#) [106-HN1-EV](#) [106-HN6-EV](#) [106-HN8-EV](#) [106-HN4-EV](#)