

Main

| | |
|-----------------------------|--|
| Product or component type | Communication card |
| Range compatibility | Altivar 312 |
| Communication port protocol | Profibus DP |
| Electrical connection | 1 connector RJ45, Modbus 1 removable screw terminal block for inputs/outputs Screw terminal block, Profibus DP |
| Transmission rate | 9600 bps, 19.2, 93.75, 187.5, 500 kbps, 1.5, 3, 6 or 12 Mbps |
| Number of addresses | 1...126 |

Complementary

| | |
|-----------------------|--|
| Input/Output number | AI2 and AI3: 2 analog input LI1...LI3: 3 logic input R2: 1 relay output |
| Communication service | CiA 402 profile Messaging via PKW periodic variables Periodic variables input : 4 PKW and 2 PZD Periodic variables output : 4 PKW and 2 PZD |
| Display type | 1 LED 1 LED for ST (status) |
| Product weight | 0.2 kg |

Environment

| | |
|--------------------------|-----------|
| RoHS EUR status | Compliant |
| RoHS EUR conformity date | 0939 |