







**HEADER PRESS-IN PIN 0.6x0.6 MM
PIN SPACING 3.5 MM / 0.138 IN 100%
PROTECTED AGAINST MISMATING
734-132/100-000 TO 734-142/100-000**

PDF DATASHEET

© 1992 - 2011 CADENAS GmbH

ITEM-NO. (ITEM-NO.)	734-135/100-000
Measured voltage (Measured voltage / V)	160
Measured shock voltage (Measured shock voltage / kV)	2.5
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	4
RM (PIN SPACING / mm)	3.5
P (NO. OF POLES)	5
Height (Height / mm)	10.3
Width (Width / mm)	19.9
Depth (Depth / mm)	8.5
COLOR (COLOR)	lichtgrau
WEIGHT (WEIGHT / g)	5.68
Comment (Comment)	L = (No. of poles - 1) x Pin Spacing + 5,9 mm
Dimensions (Dimensions)	1,15 +-0,025 mm