


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
H	—		E1	REVISED PER ECO-11-005294	02APR11	RK	HMR

D



C

B

A





RECOMMENDED PANEL CUT-OUT
MAX PANEL THICKNESS 1.7
(INFORMATIVE REFERENCE)



ALTERNATE DETAIL WITH SLOTS

SEE ALTERNATE DETAIL



NOTES:

- 1

MATERIAL:
HOUSING: THERMOPLASTIC, UL 94-V0
ALIGNMENT SLEEVES: SEE TABLE
RETENTION CLIP: SST
- 2

DUST PLUGS ARE SUPPLIED, NOT SHOWN.
- 3

FLANGELESS VERSION HAS AN OVERALL WIDTH OF 28.5 ±0.5mm
- 4

ALTERNATE DETAIL WITH SLOTS

CERAMIC	AQUA	FLANGELESS	1-1695790-1
CERAMIC	AQUA	FLANGED	1-1695790-0
METAL	AQUA	FLANGED	1695790-9
CERAMIC	BEIGE	FLANGED	1695790-8
METAL	BEIGE	FLANGELESS	1695790-7
CERAMIC	GREEN	FLANGED	1695790-6
METAL	BEIGE	FLANGED	1695790-5
CERAMIC	BLUE	FLANGED	1695790-4
CERAMIC	GREEN	FLANGELESS	1695790-3
CERAMIC	BEIGE	FLANGELESS	1695790-2
CERAMIC	BLUE	FLANGELESS	1695790-1
SLEEVE MAT'L	HOUSING COLOR	DESCRIPTION	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 22 SEP 05 CHK 30 JUN 06 APVD 30 JUN 06 A. HENGELMOLEN PRODUCT SPEC APPLICATION SPEC WEIGHT - CUSTOMER DRAWING	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH -	
MATERIAL - 1		NAME FOAC LC QUAD ADAPTER SIZE A2 CAGE CODE 00779 DRAWING NO C-1695790 RESTRICTED TO -	
		SCALE NTS SHEET 1 OF 1 REV E1	

1695790