


HIGH BREAKING CAPACITY, QUICK ACTING
CERAMIC CARTRIDGE SILVERED CAPSDOCUMENT NUMBER
TS-20-10-TDC17

F

TYPE REFERENCE
SHEET 1 OF 1

All Dimensions in mm

19.84 Max.
18.65 Min.

RATED CURRENT	IDENTIFYING COLOUR	PREFERRED RATING	MAX mV DROP @I _n	RATED VOLTAGE	
				A.C.	D.C.
1A	GREEN		500	250	250
2A	YELLOW		300	250	250
3A	BLACK		235	250	250
5A	RED		160	250	250

MANUFACTURER'S REFERENCE
RATED CURRENT
BRITISH STANDARD NUMBER
IDENTIFYING COLOUR
CUSTOMER TRADE MARK IF REQUIRED.

PERFORMANCE

CURRENT	I _n		1.6I _n		1.9I _n	
	MIN.	MAX.	MIN.	MAX.	MIN.	MAX.
TOTAL OPERATING TIME	1000 HRS	--	30 MIN	--	--	30 MIN

BREAKING CAPACITY

1000 AMPS AT 0.6 LAGGING POWER FACTOR - 250V

ENDURANCE

1000 HOURS MINIMUM AT RATED CURRENT

SERVICE TEMPERATURE

0°C TO 35° C

CONFORMS TO BS 646

Bussmann Division
Cooper (UK) Limited
Frome, Somerset BA11 1PP
England
+44 (0) 1378 464341

COOPER
Bussmann

All goods are sold and services and advice rendered in connection therewith subject only to the Company's Standard Conditions Of Sale

TDC17 (C17)



Agency Approvals: Conforms to BS646
For use in plugs and socket outlet adaptors to BS546

Dimensions (mm): 5 x 19

Breaking Capacity: 1000A at 0.6 lagging power factor - 250V

Order Code: TDC17- + Rating
Type: Fast Acting, high breaking capacity
Construction: Ceramic cartridge, silvered end caps
Ratings (A): 1, 2, 3, 5
Rated Voltage: 250V ac
Packing: 10's, 100's, 1000's

Rating (A)	Colour Code	Max. mV drop @ I_n
1	Green	500
2	Yellow	300
3	Black	235
5	Red	160

TDC180 (C180)



Agency Approvals:



The British Standard plug top fuse carries ASTA accreditation for 2 to 13A, all fuses comply with BS1362 and carry the BSI Kite Mark.

Dimensions (mm): 6.4 x 25.4

Breaking Capacity: 6000A/250V @ 0.3 - 0.4 p.f.

Order Code: TDC180 + Rating or C180 + Rating
Type: Fast Acting
Construction: Ceramic cartridge, silvered end caps
Ratings (A): 1, 2, 3, 5, 7, 10, 13
Rated Voltage: 240V ac
Packing: 10's, 100's and 1000's

Rating (A)	Colour Code	Rating (A)	Colour Code
1	Black	7	Black
2	Black	10	Black
3	Red	13	Brown
5	Black		