






Number of Contact
(View on Termination Side of Insulator)



NOTES

1. CHARACTERISTICS

Dielectric Withstanding Voltage : 1000 volts rms at sea level.

Insulation Resistance : 2000 megohms Min at 500 volts D.C.

Contact Resistance : 5 milliohms Max, 1 amps Max

2. RATING

Voltage rating : 350 volts rms at sea level

Current rating : 10 amps

3. Solder Bucket Size : 1.8 DIA.

4 A DIA. : 10.5 (8.0)

* () Sleeve at fitting

5. MATERIAL AND TREATMENT

Shell : Zinc Alloy, Nickel plated

Coupling Ring : Zinc Alloy, Nickel Plated

Insulator : Epoxy Resin

Pin Contact : Brass,

Gold Flash Over Nickel Plated

Gasket : Silicon Rubber.

Sleeve : Thermotec Plastic Elastomer



記号 SYM	変更 REVISION	品番 ITEM	部品名 DESCRIPTION	材質 MATERIAL	処理 TREATMENT	数量 QTY	備考 REMARKS
		第三角法 PROJECTION	尺度 SCALE 1/1/1	TMW TAJIMI ELECTRONICS CO.,LTD.			
		単位 UNITS mm	製造 DRAWN A Sugiyama 15 Oct '91				
		公差 TOLERANCES ON ANGLE .X .XX	設計 ENGR A Sugiyama 15 Oct '91	DATE	PRC03-12A10-3AM10.5		
		仕様書番号 SPEC NO	検図 CHK T. Waki 16 Oct '91	DATE	PRC03-10-0102		
			承認 APPD A. Nakagawa 16 Oct '91	DATE	SHEET		
					変更 REV A		