

CAP.(pf)		TOLERANCE		WORKING VOLTAGE DC		PEAK CURRENT (AMPS)	I.R. MIN. @ 100 (VDC)	DWV (VDC)	MIN. NO LOAD INSERTION LOSS (dB) @ 25°C PER MIL-STD-220				
				85°C	125°C				1 MHz	10 MHz	100 MHz	1 GHz	10 GHz
27,000		GMV		70	50	10	10 G Ω	150	10	28	45	65	70

REVISION RECORD Original Release C.O. 20000614-2-01 DIM. .038 WAS .030. S.M. 11-08-01 20011102-1-07 ADDED AND REVISED NOTES. ADDED IR & DWV S.M. 01-24-06 20060109-3-07					--TOLERANCES-- Unless Otherwise Specified	Title BUSHING STYLE EMI FILTER			
					DECIMAL ± NOTED	Drawn S.M. 06-14-00 Scale 5 X			
					ANGLES ± 	Approved T.C. 06-14-00			
					TUSONIX TUCSON, ARIZONA	A 4400-060			