



Sample photo

Order symbol: PCM 95/75 G
Product nbr: 6016332

Description: Enclosure, PC
Remarks: Grey cover

EAN:	6418074054784
El. number:	
Finland	3421394
Denmark	8212027585

Including: Base with metric knock-outs and PUR gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and wing heads for cover screws.

Dimensions:	L	W	H
mm:	100	100	75
inch:	3.9	3.9	3

Materials:

Material:	PC
Base colour:	RAL 7035
Cover colour:	RAL 7035
Cover screws material:	Polyamide
Cover screws colour:	Grey
Gasket material:	Polyurethane

Temperatures:

Short term:	-40 ... 120 °C
Continuous:	-40 ... 80 °C
Short term:	-40 ... 250 °F
Continuous:	-40 ... 175 °F

Accessories:

MIV 95	Mounting plate
B-3	DIN-35 Mounting rail

Rating:

Ingress Protection (EN 60529): IP 66/67

Impact Resistance (EN 50102): IK 08

Electrical insulation: Totally insulated

Halogen free (DIN/VDE 0472, Part 815): Yes

UV resistance: UL 508

Flammability Rating (UL 746 C 5): UL 94 5V

Glow Wire Test (IEC 695-2-1) °C: 960

NEMA Class: NEMA 1, 4, 4X, 6, 12, 13

Certificates:

Germanischer Lloyd (GL)

Underwriters Laboratories

Det Norske Veritas

Fimko

Europe EN 50298 1998

UL Canada

Gost R

