


OA280 Series



280 x 80mm
(11.0" x 3.15")



Frame	Diecast Aluminum	Operating Temperature	
Impeller	Metal	Ball Bearing	
Connection	Terminal Block, 18AWG	-40C ~ +80C	
Motor	Capacitor drive, impedance and thermally protected	Life Expectancy	
Bearing System	Dual ball	Ball Bearing	
Insulation	Class F	40,000 hours (L10 at 40C)	
Dielectric Strength	1 min at 1500 VAC, 50/60Hz	Approvals	
		UL/cUL: E170149	
		TUV: R50133561	
		Environmental	
		IP55 Rated	

Model Number	OA280AN-11-1TB18	OA280AN-22-1TB18
Part Number	280315182	280615182
Nominal Voltage (50/60Hz)	115VAC	230VAC
Voltage Range	100 ~ 125VAC	200 ~ 240VAC
Rated Power	112 / 148 W	119 / 158 W
Nominal Current	1.0 / 1.5 A	0.59 / 0.82 A
Rated Speed (RPM) (50/60Hz)	2550 / 2700	2550 / 2700
Airflow (CFM) (50/60Hz)	1090 / 1130	1090 / 1130
Noise Level (dB)	68 / 70	68 / 70
Max. Static Pressure (50/60Hz)	0.78" H ₂ O / (0.65")	0.78" H ₂ O / (0.65")