

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0982680841](#)
Status: **Active**
Overview: [Premo-Flex Cable Jumpers](#)
Description: 1.25mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 127.00mm Cable Length, Tin (Sn) Plating, 15 Circuits

Documents:

Drawing (PDF)	Datasheet (PDF)
Packaging Specification PK-98268-001-001 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Cable
Series	98268
Comments	Contacts on opposite sides, Type D
Crimp Quality Equipment	Yes
Overview	Premo-Flex Cable Jumpers
Product Name	Premo-Flex FFC Jumper
UPC	800756945187

Physical

Cable Length	127.00mm
Circuits (Loaded)	15
Material - Plating Mating	Tin
Packaging Type	Bag
Pitch - Mating Interface	1.25mm
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable

Electrical

Current - Maximum per Contact	1.4A
Voltage - Maximum	60V AC

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-98268-001-001
Sales Drawing	SD-98268-001



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[98268 Series](#)

Mates With

Molex FFC – FPC connector. Be sure to match like plating.

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION