

Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click ☐ to remove) Search Tips [?](#)

☒ Text Search: 'F5PE10K-NM4'

Your search criteria matched only one product, shown below

F5PE10K-NM4



- Pass all TIA/EIA-568-B.3 performance requirements
 - Insertion loss per connection: 0.10dB typical; 0.30dB maximum
 - Include color-specific keys with positive and negative keying features to mechanically and visually distinguish connections to prevent unauthorized mating with unlike keyed or non-keyed adapters
 - Part of a complete Keyed LC System that includes *Opti-Core*® Patch Cords and Pigtails, *OptiCam*® Pre-Polished Cam Connectors, *Opticom*® Fiber Adapter Panels (FAPs), and *Mini-Cor*® Adapter Modules
 - Factory terminated and 100% tested for insertion loss
 - Insertion loss data recorded for every multimode patch cord
 - Lifetime traceability of test data to a Q.C. number on each patch cord
 - Highest quality flame retardant fiber optic cable with tight-buffered coating on each optical fiber
- Additional lengths and availability: Keyed LC patch cords and pigtails are available in 1m – 10m lengths in 1m increments, and 15m, 20m, and 30m lengths. For other lengths, contact*

Customer Service for actual lead times.

Additional keyed colors include the following: G– Violet, H– Aqua, J– Rose, K– Slate, L– Brown, P– White, Q– Charcoal, R– Lavender, S– Peach, T– Steel Blue, V– Maroon and W– Mint.

• Part Number	F5PE10K-NM4
• RoHS Compliancy Status	Compliant
• Note	Intended for use in fixed installations which are outside the scope of RoHS.
• Part Description	LC (keyed K - Slate) to pigtail, plenum rated, OM2, patch cord, 1.6mm jacketed cable (one duplex keyed LC connector on one end and pigtail on other end)
• Product Type	Keyed LC Patch Cords
• Length (m)	4
• Fiber Compatibility	50/125µm
• Fiber Type	Jacketed
• Connector 1 Type	Keyed LC (K-Slate)
• Connector 2 Type	Pigtail
• Flammability Rating	Plenum (OFNP)
• Key Type and Color	Keyed K - Slate
• Pricing Description	Keyed LC (K-Slate) to pigtail, OM2, OFNP, 4M
• Min. Order UOM	PC
• Min. Order Qty.	1
• BOM Qty. (# of Pkgs.)	0
• Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.