



Conformity to RoHS Directive

SHAPES AND DIMENSIONS



SOLDER RESIST




Dimensions in mm

Frequency range(Pass band)		2400 to 2500MHz
Insertion loss	[+25°C]	2.5dB max.
Return loss	[2400 to 2500MHz]	10dB min.
	[880 to 915MHz]	40dB min.
	[1710 to 1850MHz]	40dB min.
	[1850 to 1910MHz]	40dB min.
Attenuation	[1920 to 1990MHz]	40dB min.
	[2110 to 2170MHz]	26dB min.
	[4800 to 5000MHz]	30dB min.
	[7200 to 7500MHz]	30dB min.
Temperature range	Operating	-40 to +85°C
	Storage	-40 to +85°C


- 001-02 / 20130901 / rf bpf dea202450bt-3201b2 en.

FREQUENCY CHARACTERISTICS


INSERTION LOSS



RETURN LOSS



ATTENUATION



VSWR

