

- RC-16P1N121I00 - 1600529

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable connector, with Pg9 connection thread, straight, shielded: No, Screw locking, M23, Number of positions: 16, Type of contact: Male connector, Solder connection, Cable diameter: 6.5 mm ... 9.5 mm

The figure shows the 12-pos. product version, with standard DIN cable gland



Key commercial data

Packing unit	1 pc
Custom tariff number	74153300
Country of origin	Germany

Technical data

Product type	Circular connector (cable-side)
Cable diameter	6.5 mm ... 9.5 mm
Coding	N
Type	Cable connector, with Pg9 connection thread
Number of positions	16
Thread	M23
Rated voltage (IEC)	150
Rated current (IEC)	8
Knurl material	Metal
Shielding	No
Signal type	Signal
Connection method	Solder connection

- RC-16P1N121I00 - 1600529

Classifications

eCl@ss


eCl@ss 4.0	272607xx
eCl@ss 4.1	272607xx
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260708

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC001121

Drawings

Schematic diagram



Dimensioned drawing

