


Lamp Specification

Wamco Part No.	Envelope Size	Base Type	Rating	Filament Shape
WL-55	G4-1/2	BA9s	7V .41A	C-2R

Test Volts	Current (A)			Light Output (MSCP)			Life Hours
	Min.	Nom.	Max.	Min.	Nom.	Max.	
7	.369	.410	.451	1.50	2.00	2.50	500 Hrs

Dimensional Characteristics:

- L.C.L. = .56"
(14.2mm)
 - Base = Nickel-plated
Brass Construction.
- ANSI Standard No. 55



			Title: G4-1/2 Miniature Bayonet Base Lamp 7V .410A Vacuum	
Drawn	07/13/10	CI	Notes: Unless otherwise specified, all dimensions are in inches.	
Checked	07/13/10	EB		
Approved	07/14/10	EB		
			Rev: 1	