




Field Interface Modules



Passive - 2 wire
16 Channel
Output
GE Fanuc



Passive - 2 wire
16 Channel
Output
GE Fanuc



Technical Data

Type	RS PLC 16PT (4x4)			RS PLC 16PT (4x4)
Part number	998132	120 VAC	IC697MDL340	998074
	998142	24-48 VDC	IC697MDL740	
Rated voltage	See Above			24-120 VAC/DC
Rated current	2.0 A per channel / 4.0 A per group of 4			3.0 A per channel / 3.0 A per group of 4 / 12.0 A per module
Cable connection	(1) 1 x 40 pin IDC			(1) 1 x 40 pin IDC
LED Indicators	No			No
Operating Temperature	0°C...+50°C			0°C...+50°C
Storage Temperature	-20°C...+60°C			-20°C...+60°C
Dimensions LxWxH mm	113 x 70 x 59			113 x 70 x 59
Terminal Wire Size	#26...14 AWG			#26...14 AWG
Terminal Type	Screw Clamp			Screw Clamp
Approvals				

Wiring Schematics

