




Left Side

Connector(s): LC-Duplex Secure
Mode: MM
Housing Color: Red
Geom. Spec: N/A

Fiber Path

A - _____ - B
B - _____ - A

Right Side

Connector(s): SC-Duplex
Mode: MM
Housing Color: Beige
Geom. Spec: N/A

Notes:

- 1 Product and Processing must meet requirements of Tyco Electronics Standard 230-702
- 2 Includes dust caps (not shown on print).
- 3 IL tested at 1300nm.
- 4 Label 2 will not be present on any cable assembly less than 5 meters long.

	A	Rev Per EC#	None	7/30/2007	-	DF			
P	LTR	REVISION RECORD		DATE	DN	APVD			

DIMENSIONS:
meters

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 P.L.C. ± .
1 P.L.C. ± .
2 P.L.C. ± .
3 P.L.C. ± .
4 P.L.C. ± .

Restricted To:

DWG Cable Assy Configurator		MATERIAL -	HEAT TREAT -	
CHK Dave Fennell	AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
APVD Dave Fennell				
NAME FO C/A - 2 fiber, 50/125, OFNP (Plenum) jacket, LC-Duplex Secure to SC-Duplex				
SCALE NTS	SIZE A2	DRAWING NO C- 1905002	SHEET 1 of 4	REV A

THIS DRAWING IS A CONTROLLED DOCUMENT.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

A	LTR	Rev Per EC# None	7/30/2007	-	DF			
P	LTR	REVISION RECORD	DATE	DIN	APVD			

Qty	U of M	Description	Item No
2	piece	Trace Label	10
2	piece	CONN SUBASSY, MM, SC 1.6MM	9
4	piece	Eyelet/Shrink tube assembly - White	8
2	piece	SC Duplex Clip	7
2	piece	2.5mm ferrule cover	6
2	piece	SC Simplex Housing, Beige	5
AR	meter	2 fiber, 50/125, 1.8mm, Twinzip, Red, OFNP (Plenum)	4
2	piece	LC Connector Assy, 1.6mm-2.0mm, MM	3
1	piece	LC Duplex clip, black	2
4	piece	LC, SC, FC Straight Boot, Beige	1

DIMENSIONS: meters  <table><tr><td>0 P.C.</td><td>± .</td></tr><tr><td>1 P.C.</td><td>± .</td></tr><tr><td>2 P.C.</td><td>± .</td></tr><tr><td>3 P.C.</td><td>± .</td></tr><tr><td>4 P.C.</td><td>± .</td></tr></table>			0 P.C.	± .	1 P.C.	± .	2 P.C.	± .	3 P.C.	± .	4 P.C.	± .	DIN Cable Assy Configurator		MATERIAL -		HEAT TREAT -	
			0 P.C.	± .														
1 P.C.	± .																	
2 P.C.	± .																	
3 P.C.	± .																	
4 P.C.	± .																	
OR Dave Fennell		APVD Dave Fennell		AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608														
NAME FO C/A - 2 fiber, 50/125, OFNP (Plenum) jacket, LC-Duplex		Secure to SC-Duplex																
Restricted To:			NTS	SIZE A2	DRAWING NO C- 1905002	SHEET 2 of 4	REV A											

- Restricted To:

THIS DRAWING IS A CONTROLLED DOCUMENT

DWG NO

CAC Customer Layout Rev: D

	A	Rev Per EC# None	7/30/2007	-	D
P	LTR	REVISION RECORD	DATE	DIN	AP

DIMENSIONS; meters		TOLERANCES UNLESS OTHERWISE SPECIFIED	
	0 PLC	±	-
	1 PLC	±	-
	2 PLC	±	-
	3 PLC	±	-
	4 PLC	±	-

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANY OTHERS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

THIS DRAWING IS A CONTROLLED DOCUMENT.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

8

7

6

5

4

3

2

1

Label 1

Per specification 107-1645-1



Trace # - Bar Code

XXXXXXXXXXXXXXXXXX

Trace # - Human Readable

Part Number

Country of Origin

This label is used on all lengths on this drawing.

Label 2

Per specification 107-1645-1



Trace # - Bar Code

XXXXXXXXXXXXXXXXXX

Trace # - Human Readable

Part Number

Country of Origin


This label is used on all lengths on this drawing.

	A	Rev Per EC#	None	7/30/2007	-	DF			
P	LTR	REVISION RECORD		DATE	DIN	APVD			

DIMENSIONS:
meters

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 P.L.C. ± .
1 P.L.C. ± .
2 P.L.C. ± .
3 P.L.C. ± .
4 P.L.C. ± .

Restricted To:

DWG Cable Assy Configurator		MATERIAL	HEAT TREAT	
CHK	Dave Fennell			
APVD	Dave Fennell			
NAME FO C/A - 2 fiber, 50/125, OFNP (Plenum) jacket, LC-Duplex Secure to SC-Duplex				
SCALE NTS	SIZE A2	DRAWING NO. C-1905002	SHEET 4 of 4	REV A