

Sta-Kon®



T&B Catalog Number:

F4006

UPC Number:


78621072964

Description:

Insulated Nylon Ferrule for Wire Size 24,
Wire Size 0.25 mm², Length 0.413 inches,
Yellow

Status:

Active



WEB_USE

-T&B Product Line	029
-US Cutsheet PDF Catalog Link	http://www-public.tnb.com/contractor/docs/stakon.pdf

Features

-	Ferrules ensure reliable electrical connections when terminating conductors in screw clamp terminal blocks.
---	---

General

-Ferrule Type	Insulated
-Insulation Type	Insulated Nylon
-Material	Copper
-Finish	Electro -Tin Plated
-Color	Yellow
-Wire Range	24
-Wire Size (mm ²)	.25

Dimension Information

-A (mm)	10.5
-B (mm)	6.0
-Diameter C (inches)	.031
-Diameter C (mm)	0.8
-Diameter D (inches)	.079
-Diameter D (mm)	2.0
-E (mm)	.25
-A (inches)	.413
-B (inches)	.236
-E (inches)	.010

Specifications

-Temperature Rating	105°C
-Voltage Rating	300V
-Flammability Rating	UL 94 V-2

Tooling

-Application Tools	T3, ERG2
-Recommended Tool	T3, ERG4

Packaging

-T&B Order Multiple	500
-T&B Inner Pack	500
-Package in Units	10000
-T&B Sold in UOM	Each
-T&B Weight Per UOM	0.2 lbs. per 1000

Application Support

-T&B Sales Drawings	wsd-000402
-Overview	Available on Website

-Wire Guide Tables

Available on Website

Notes

-

Ferrule dimensions conform to DIN 46228, Part 4.

Certifications

-RoHS Compliance

Yes

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com