

REV. U

UNLESS OTHERWISE NOTED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:


ONE PLACE DECIMALS $\pm .1$ [.3] THREE PLACE DECIMALS $\pm .005$ [.13]
 TWO PLACE DECIMALS $\pm .01$ [.3] FOUR PLACE DECIMALS $\pm .0020$ [.051]

ANGLES
 $\pm 2^\circ$

TITLE:
 LOW PROFILE
 SOCKET STRIP

DWG NO:
 SLW-1XX-01-X-X

SHEET 1 OF 1



POSITION SPECIFICATION
 -01 THRU -50 PER ROW
 "A" = NO. OF POS. x .100 [2.54]




CONTACT STYLE
 -01: USE C-28-X

ROW SPECIFICATION
 -D: DOUBLE (USE SLW-50-D)
 -S: SINGLE (USE SLW-50-S)

PLATING SPECIFICATION
 -G: GOLD-SPECIFY -G IN CONTACT SUFFIX -X
 -T: TIN-SPECIFY -T IN CONTACT SUFFIX -X
 -S: SELECTIVE GOLD, MATTE TIN TAIL-SPECIFY -S IN CONTACT SUFFIX -X
 -F: FLASH SELECTIVE GOLD-SPECIFY -F IN CONTACT SUFFIX -X
 -H: HEAVY GOLD-SPECIFY -H IN CONTACT SUFFIX -X
 -L: LIGHT SELECTIVE GOLD, MATTE TIN TAIL-SPECIFY -L IN CONTACT SUFFIX -X

NOTES:

1. MIN PUSHOUT FORCE: 1 lb.
2. MAX BOW: .005 in/in [mm/mm], .025 [.64]
3. CUT END WALLS TO BE .012 [.30] MIN.
4. (C) REPRESENTS CRITICAL DIM.
 FOR STATISTICAL PROCESS CONTROL
 .010 [.25] MAX CUT FLASH
5. NO TUBE PACKAGING REQUIRED



PLOT SCALE: 1=1

samtec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
 PHONE (812) 944-6733 P.O. BOX 1147
 CODE 55322

MADE BY: PURVIS 9-4-87
 CHECKED BY: McCARTIN

ENG.
 APPROVAL
 DEM

SLW-1XX-01-X-X
 SHEET 1 OF 1

PROPRIETARY NOTE
 THIS DOCUMENT CONTAINS INFORMATION
 CONFIDENTIAL AND PROPRIETARY TO
 SAMTEC INC. AND SHALL NOT BE
 REPRODUCED OR TRANSMITTED IN
 ANY FORM OR BY ANY MEANS
 ELECTRONIC OR MECHANICAL
 INCLUDING PHOTOCOPYING, RECORDING,
 OR BY ANY INFORMATION STORAGE
 AND RETRIEVAL SYSTEM WITHOUT THE
 WRITTEN CONSENT OF SAMTEC INC.

Do not scale
 from this print