


Dimensions (In.)
(except where noted)



Specifications:

- Input: 120V 60Hz
- Output: 15VAC 400mA
- Primary voltage: 120VAC 60Hz
- Primary exciting current: 30mA max.
- Secondary unloaded voltage $\pm 5\%$: 19VAC
- Secondary loaded voltage $\pm 5\%$: 15VAC
- Secondary loaded current: 400mA
- Insulation resistance: primary-secondary 500VDC 100M Ω min.
primary-core 500VDC 100M Ω min.
- Dielectric strength: primary-secondary primary-core 1250VAC for 1 minute
secondary-core 500VAC for 1 minute
- Temperature rise: @ rated loading 65C max.
- Impregnation: varnish

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Xicon:

41AC415