

1			2			3			4			5			6			7			8					
插頭部件 (Plug Component)						頭部剥皮尺寸 (Dimensions)			線材規格 (Wire Stlys)			尾部剥皮尺寸 (Dimensions)			尾插部件 (Connector Component)											
顏色(Color)		零件描述(Component)		Qty.		內剥(Strip)		外剥(ROJ)		顏色(Color)		SVT 18AWGx3C			外剥(R.O.J)		內剥(Strip)		顏色(Color)		規格描述(Instruction)		Qty.		顏色(Color)	
35P 黑色 (Black)		ME-301 (NEMA 5-15P)		1		6 ⁺¹ ₋₀		22 ± 2		黑/Black(L)		105°C 黑色 (BLACK)			16 ±1		5 ⁺¹ ₋₀		黑/Black(L)		FM-302L (IEC 60320, C13)		1		35P 黑色 (Black)	
鍍鎳 (Nickel-Plated)		φ4.75 圓管端子 (Earth Pins Terminal)		1		6 ⁺¹ ₋₀		22 ± 2		白/White(N)		Length : 2000±50 (79"±2")			16 ±1		5 ⁺¹ ₋₀		白/White(N)		2.0*4.0 方管端子 (2.0*4.0 Receptacle Terminal)		3		銅本色 (Brass-Natural)	
鍍鎳 (Nickel-Plated)		6.3*1.5 單片圓頭端子 (Solid Blades)		2		6 ⁺¹ ₋₀		22 ± 2		綠/Green(E)					16 ±1		5 ⁺¹ ₋₀		綠/Green(E)		GA005-5 兩件式內模 (2.0*4.0 Serial Housing)		1		米白色 (Off-White)	
黑色 (Black)		301-1 兩件式內模 (301-1 Inner Body)		1																						

Earth Ground (Green)

φ4.75±0.15

ME-301 (NEMA 5-15P)
(Dimensions of Plug Face)

SVT 18AWGx3C截面圖 (Wire Cross-Section)

Filler Strip

PVC Insulation Thickness 0.46(>0.41mm)

Overall Diameter 2.10±0.08mm

Copper Conductor 41/0.160±0.003mm

Diameter 1.18mm (Approx.)

Cotton Parer ¼ Lap Warp

PVC Jacket Thickness 0.84mm(>0.76mm)

Overall Diameter 6.3±0.15mm

Green

White

Black

B-C2 扎線圖示 (Tied Loop Hank Detail)

200±30

FM-302L (IEC 60320, C13, RA)
(Dimensions of Connector Face)

24±0.15

23±0.15

15.5±0.15

43.5±0.25

(N) White

(E)

(L) Black

REV	DATE	REVISE CONTENT	NOTE:
A	08/29-2012	The first edition is issued and drawing.	1. Hi-Pot Test : 1500V/1Sec ; <0.5mA. 2. Insulation Resistance Test : DC 500/min>100 meg-ohm. 3. Continuity & Polarization Test : No short circuit, break circuit, displacement. 4. Each end terminal shall be capable of withstanding a pull of 25lbs for 1 minutes without loosening. 5. Strain relief shall be capable of withstanding a pull of 35lbs for 1 minutes without loosening. 6. All material according to Non-toxic standard.(Material must be RoHS compliant.) 7. "FMC" logo maybe present on C13.

線材印字 (Wire Printed)		充麻, 油墨印字 (Fillers, Printing Ink)		CnC Tech, LLC Industrial Cable and Connector Technology			
包裝方式 (Packing)		DRAWN Chu8.		CUSTOMER		CnC	
Tied Hank	See Hank Detail	DATE 08/29-2012		P/N No.		800-18-1-2-SVT0-BL-00200	
Carton Size	480 x 320 x 180			MATERIAL		PVC	UNIT mm
Pack Number	75pcs/UL Laster Labels			Customer Approval			
Carton Print	See Purchase Order						
TYPE	NEMA 5-15P to IEC 60320 C13 Right Angle Power Supply Cord						
DRAWNING NO.	098MM978	REV	A				