

567X

Flash Cards



Releasing the Power of Photography!

Pretec's CF567X Card marks a new breakthrough in the area of flash memory cards providing unmatched capacities up to 128GB, at a high speed of 85MB per second.

Made with the professional photographer in mind, these cards provide the speed and capacity needed to work fast and spontaneous, while keeping up high performance under even the harshest conditions. The metal housing provides extensive ruggedness making the card resistant to external impacts. Be it in the studio, on the streets, or in the field, the high transfer speed of these responsive cards allows rapid capture of high-resolution photos, always being ready for the next shot. Take more pictures in the same time (continuous high-speed shooting), view images faster on the screen of your camera, and minimize download times to your computer.

Pretec furthermore provides a wide range of speed/capacity combinations to offer solutions for the advanced amateur and photo enthusiast using high-end digital cameras.

Blazing Speed

Highest Capacity

Rugged Construction



Features:

- Large capacity range: 16GB/32GB/64GB/128GB
- High read/write speed up to 85MB* per second
- Low power consumption with automatic power management
- Zero-power data retention, no batteries required
- Supports Ultra DMA mode 0-6

* Speed performance may vary depending on different testing environment.



567X

COMPACTFLASH CARD SERIES

Specifications

Dimensions

CompactFlash™ Type I:

36.4mm(L) x 42.8mm(W) x 3.3mm(H)

Weight: ±15g

CompactFlash™ Type II:

36.4mm(L) x 42.8mm(W) x 5.0mm(H)

Weight: ±23g

Performance

Max. data transfer rate:

100MB/sec (667X) ; 85MB/sec (567X);

65MB/sec (433X) ; 35MB/sec (233X);

12~20MB/sec (Standard)

Command to DREQ : 2ms (Min.)

Reset to Ready : 100ms (Min.)

Sleep to idle : 2ms (Min.)

Storage Capacities

CF 667X: 8GB/16GB/32GB

CF 433X: 8GB/16GB

CF 567X: 16GB/32GB/64GB (Type I)
128GB (Type II)

CF 233X: 1GB ~ 64GB

CF Standard: 512MB ~ 8GB

Operating Voltage

3.3V ±5% ; 5V ±10%

System Compatibility

Professional Digital Cameras


PDA, PCA, Palmtops, Handheld devices

Set-Top boxes

Operation temperature : -20°C ~ +85°C

Relative humidity : 95% (Max.)

The Fastest CompactFlash™ Card



Ordering Information

667X CF Card (Metal Housing)

8GB	CFS608G	471-800041-297-1
16GB	CFS616G	471-800041-298-8
32GB	CFS632G	471-800041-299-5

567X CF Card (Metal Housing)

16GB	CFS516G	471-800041-373-2
32GB	CFS532G	471-800041-374-9
64GB	CFS564G	471-800041-375-6
128GB	CFS5128	471-800041-376-3

433X CF Card (Metal Housing)

8GB	CFS408G	471-800041-169-1
16GB	CFS416G	471-800041-170-7

233X CF Card

1GB	CFS201G	471-096967-916-7
2GB	CFS202G	471-096967-917-4
4GB	CFS204G	471-096967-918-1
8GB	CFS208G	471-096967-919-8
16GB	CFS216G	471-096967-920-4
32GB	CFS232G	471-096967-966-2
48GB	CFS248G	471-096967-965-5
64GB	CFS264G-34	471-800041-053-3

Standard CF Card

512MB	CFSS12	471-096967-949-5
1GB	CFSS01G	471-096967-950-1
2GB	CFSS02G	471-096967-951-8
4GB	CFSS04G	471-096967-952-5
8GB	CFSS08G	471-800041-250-6

Package contents

