

Microphone

Electret Condenser Microphone
analog-Omnidirectional
KECG2742PBL





Shape

KECG2742PBL




Sensitivity(dB)	-42±3dB
Operating Voltage (V.D.C.)	2
Impedance (Ω)	2.2K
Rated Voltage (V.D.C.)	10
Sensitivity Reduction(Hz)	-3dB@f=1KHz,1Pa,Vs=2.0V.D.C. to 1.5V.D.C.
Frequency Range(Hz)	20 ~ 20,000
Max. Current Consumption (mA)	0.5@Vs=2.0V.D.C. RL=2.2KΩ
S/N Ratio(dBA)	58

Dimension

CONTACT TYPE**TERMINAL TYPE****PIN TYPE****WIRE TYPE**

Tol : ± 0.5 Unit : mm

∴ Characteristic / Schematic Diagram



TOP ▲