


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	MATERIAL	LABEL SIZE inches [mm]	"A"	"B"	"C"	LABELS PER ROW	LABELS PER PKG.
N100X125CBT	GMC	1.000 [25.4] X 1.250 [31.8]	1.250 [31.8]	1.350 [34.3]	1.075 [27.3]	3	5000
N100X150CBT	GMC	1.000 [25.4] X 1.500 [38.1]	1.500 [38.1]	1.600 [40.6]	1.075 [27.3]	3	5000
N100X175CBT	GMC	1.000 [25.4] X 1.750 [44.5]	1.750 [44.5]	1.850 [47.0]	1.075 [27.3]	3	2500



1. SEE MFG. DRAWING NO. A61258.
2. MILLIMETER ARE IN [].

100472JR_C10295_N100XNUMCBT_00.PRT

PANDUIT CORP. TINLEY PARK, ILLINOIS

OPTIMUM N100X***CBT
THERMAL TRANSFER LABELS

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .031 (.XXX) ± .005
(.XX) ± .015 ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

	MAT'L:
--	--------

NTS

DATE	10-1-04
------	---------

SEE TABLE

C10295

DWG
A
SIZE

0	10-1-04	RVU		DRAWING RELEASED.
---	---------	-----	--	-------------------

0000	R
------	---

R

REV	DATE	BY	CHK	DESCRIPTION
-----	------	----	-----	-------------

ECN	-	R	CUST	SUP
-----	---	---	------	-----

CUST	SUP
------	-----