


Date	SYM	REVISION RECORD	AUTH	DR.	CK.
08/01/14	C	UPDATED TO ROHS 2 COMPLIANT	T.B.	B.S.	




# SPECIFICATION:

## 1. MATERIAL:

HOUSING : BLACK POLYPROPYLENE  
FLAMMABILITY RATING -UL94-HB, UL FILE NO. E216959  
TEMPERATURE RANGE: -10°C to +100°C  
RIVETS: BRASS, NICKLE PLTD.  
WIRE: 26 AWG, 152.4mm LONG  
SPRING: SPRING STEEL, NICKLE PLTD.  
CONTACT RESISTANCE: UNDER 50mΩ FOR +/- CONTACTS PER EIA-540J000  
ROHS 2 COMPLIANT

## MOUNTING INSTRUCTION:

USE 2-56 MACHINE SCREWS OR EYELETS 0.089" OD BY 0.15" FLANGE STIMPSON GS-3 SERIES OR EQUIVALENT. ALSO ADHESIVES AND DOUBLE SIDED TAPES WORK WELL.

Tolerance (Except as noted)	 Memory Protection Devices, Inc 200 Broad Hollow Road, Farmingdale, New York 11735		
decimal ±.5 (.020)			Scale Drawn By B.S. Approved By T.B.
Fractional ± .8 (.030)	Title 8 "D" CELL HOLDER WITH SOLDER LUGS		
Angular ± 3°	Date 08/01/14	Drawing Number BH28DL	